

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246084

Luminaire Tested: P3A05R259024DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246084
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R259024DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 462.0 lumens
Efficiency: N/A
Efficacy: 64.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246084

CATALOG NUMBER: P3A05R259024DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1246084

CATALOG NUMBER: P3A05R259024DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	78		84	80	77		83	79	77		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	296358
5°	276491
10°	221483
15°	150353
20°	90985
25°	53205
30°	30308
35°	16677
40°	8845
45°	4652
50°	2695
55°	2026
60°	1754
65°	1816
70°	1667
75°	1525
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4652 cd/sqm

TEST NUMBER: P1246084

CATALOG NUMBER: P3A05R259024DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.5	24.1
10°-20°	182.1	39.4
20°-30°	104.0	22.5
30°-40°	41.1	8.9
40°-50°	12.6	2.7
50°-60°	5.0	1.1
60°-70°	3.3	0.7
70°-80°	1.9	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	397.6	86.1
0°-40°	438.7	95.0
0°-60°	456.2	98.8
0°-90°	462.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	462.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1352	
5°	1256	111
15°	662	182
25°	220	104
35°	62	41
45°	15	13
55°	5	5
65°	4	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1246084

CATALOG NUMBER: P3A05R259024DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1351.5
1°	1348.8
2°	1337.8
3°	1318.4
4°	1291.4
5°	1256.1
6°	1214.6
7°	1167.8
8°	1113.5
9°	1057.9
10°	994.7
11°	932.5
12°	864.1
13°	796.5
14°	727.2
15°	662.3
17.5°	513.5
20°	389.9
22.5°	292.7
25°	219.9
27.5°	162.9
30°	119.7
32.5°	86.5
35°	62.3
37.5°	44.2
40°	30.9
42.5°	21.2
45°	15.0
47.5°	10.6
50°	7.9
52.5°	6.2
55°	5.3
57.5°	4.9
60°	4.0
62.5°	3.5
65°	3.5
67.5°	3.1
70°	2.6
72.5°	2.2
75°	1.8
77.5°	1.3
80°	0.9
82.5°	0.9
85°	0.4
87.5°	0.4



TEST NUMBER: P1246084

CATALOG NUMBER: P3A05R259024DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)