

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301999

Luminaire Tested: P3AS17R60W2N902750DE010 E3CD1MB_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902750DE010 E3CD1MB_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,
E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1400.0 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301999
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3CD1MB_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1301999

CATALOG NUMBER: P3AS17R60W2N902750DE010 E3CD1MB_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	10.0
10°-20°	403.9	28.8
20°-30°	471.1	33.6
30°-40°	304.0	21.7
40°-50°	68.1	4.9
50°-60°	6.8	0.5
60°-70°	3.2	0.2
70°-80°	1.9	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1015.3	72.5
0°-40°	1319.3	94.2
0°-60°	1394.2	99.6
0°-90°	1400.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1400.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1525	
5°	1458	140
15°	1475	404
25°	1030	471
35°	492	304
45°	75	68
55°	5	7
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1301999

CATALOG NUMBER: P3AS17R60W2N902750DE010 E3CD1MB_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1524.6
2.5°	1499.7
5°	1458.5
7.5°	1456.4
10°	1484.5
12.5°	1502.9
15°	1474.8
17.5°	1390.3
20°	1266.9
22.5°	1138.0
25°	1029.7
27.5°	923.6
30°	798.0
32.5°	650.8
35°	491.6
37.5°	335.7
40°	211.1
42.5°	126.7
45°	74.7
47.5°	43.3
50°	22.7
52.5°	7.6
55°	5.4
57.5°	4.3
60°	4.3
62.5°	3.2
65°	3.2
67.5°	3.2
70°	2.2
72.5°	2.2
75°	2.2
77.5°	1.1
80°	1.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0

(END OF REPORT)