

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246138

Luminaire Tested: P3A05R359024DE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1246138  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R359024DE010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 357.1 lumens  
Efficiency: N/A  
Efficacy: 49.6 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246138  
CATALOG NUMBER: P3A05R359024DE010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1246138  
 CATALOG NUMBER: P3A05R359024DE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44			44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	81550
5°	79815
10°	74748
15°	67106
20°	58362
25°	49745
30°	41677
35°	33194
40°	23988
45°	15195
50°	8290
55°	5735
60°	5438
65°	5033
70°	4809
75°	4151
80°	3915
85°	3271

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15195 cd/sqm



TEST NUMBER: P1246138  
 CATALOG NUMBER: P3A05R359024DE010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.7	9.5
10°-20°	82.3	23.0
20°-30°	94.3	26.4
30°-40°	76.9	21.5
40°-50°	38.8	10.9
50°-60°	14.4	4.0
60°-70°	9.7	2.7
70°-80°	5.4	1.5
80°-90°	1.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	210.3	58.9
0°-40°	287.2	80.4
0°-60°	340.4	95.3
0°-90°	357.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	357.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	372	
5°	363	34
15°	296	82
25°	206	94
35°	124	77
45°	49	39
55°	15	14
65°	10	10
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1246138  
CATALOG NUMBER: P3A05R359024DE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	371.9
1°	371.5
2°	370.6
3°	368.8
4°	366.2
5°	362.6
6°	358.2
7°	353.8
8°	348.1
9°	342.3
10°	335.7
11°	328.7
12°	321.2
13°	312.8
14°	304.0
15°	295.6
17.5°	273.1
20°	250.1
22.5°	226.8
25°	205.6
27.5°	184.8
30°	164.6
32.5°	144.3
35°	124.0
37.5°	103.7
40°	83.8
42.5°	65.3
45°	49.0
47.5°	35.3
50°	24.3
52.5°	17.6
55°	15.0
57.5°	13.7
60°	12.4
62.5°	11.0
65°	9.7
67.5°	8.4
70°	7.5
72.5°	6.2
75°	4.9
77.5°	4.0
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.9



TEST NUMBER: P1246138  
CATALOG NUMBER: P3A05R359024DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)