

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302050

Luminaire Tested: P3AS17R60W2N902750DE010 E3DL1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902750DE010 E3DL1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1256.0 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302050
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DL1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302050
 CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DL1LI_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 125.7 | 10.0 |
| 10°-20° | 326.6 | 26.0 |
| 20°-30° | 372.2 | 29.6 |
| 30°-40° | 264.0 | 21.0 |
| 40°-50° | 119.8 | 9.5 |
| 50°-60° | 25.4 | 2.0 |
| 60°-70° | 12.2 | 1.0 |
| 70°-80° | 7.6 | 0.6 |
| 80°-90° | 2.6 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 824.4 | 65.6 |
| 0°-40° | 1088.4 | 86.7 |
| 0°-60° | 1233.6 | 98.2 |
| 0°-90° | 1256.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1256.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1352 | |
| 5° | 1335 | 126 |
| 15° | 1177 | 327 |
| 25° | 818 | 372 |
| 35° | 420 | 264 |
| 45° | 150 | 120 |
| 55° | 19 | 25 |
| 65° | 12 | 12 |
| 75° | 7 | 8 |
| 85° | 2 | 3 |
| 90° | 0 | |



TEST NUMBER: P1302050
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1352.5 |
| 2.5° | 1347.7 |
| 5° | 1334.6 |
| 7.5° | 1311.9 |
| 10° | 1280.9 |
| 12.5° | 1236.7 |
| 15° | 1177.0 |
| 17.5° | 1101.8 |
| 20° | 1013.5 |
| 22.5° | 918.0 |
| 25° | 817.7 |
| 27.5° | 715.1 |
| 30° | 612.4 |
| 32.5° | 514.5 |
| 35° | 420.2 |
| 37.5° | 336.6 |
| 40° | 261.4 |
| 42.5° | 198.2 |
| 45° | 150.4 |
| 47.5° | 112.2 |
| 50° | 74.0 |
| 52.5° | 34.6 |
| 55° | 19.1 |
| 57.5° | 16.7 |
| 60° | 15.5 |
| 62.5° | 14.3 |
| 65° | 11.9 |
| 67.5° | 10.7 |
| 70° | 9.6 |
| 72.5° | 8.4 |
| 75° | 7.2 |
| 77.5° | 6.0 |
| 80° | 4.8 |
| 82.5° | 3.6 |
| 85° | 2.4 |
| 87.5° | 1.2 |
| 90° | 0.0 |

(END OF REPORT)