

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246173

Luminaire Tested: P3A05R409024DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R409024DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 324.0 lumens
Efficiency: N/A
Efficacy: 45.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246173
CATALOG NUMBER: P3A05R409024DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1246173
 CATALOG NUMBER: P3A05R409024DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	91	94	92	89	92	89	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69			
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	62	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100891
5°	98833
10°	92027
15°	80205
20°	64639
25°	48462
30°	34056
35°	22326
40°	13511
45°	8063
50°	4810
55°	3861
60°	3465
65°	2958
70°	2821
75°	2203
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8063 cd/sqm



TEST NUMBER: P1246173
 CATALOG NUMBER: P3A05R409024DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.7	12.9
10°-20°	97.3	30.0
20°-30°	91.7	28.3
30°-40°	53.0	16.4
40°-50°	21.1	6.5
50°-60°	9.4	2.9
60°-70°	5.8	1.8
70°-80°	3.0	0.9
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.7	71.2
0°-40°	283.8	87.6
0°-60°	314.2	97.0
0°-90°	324.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	324.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	460	
5°	449	42
15°	353	97
25°	200	92
35°	83	53
45°	26	21
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1246173
CATALOG NUMBER: P3A05R409024DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	460.1
2.5°	457.4
5°	449.0
7.5°	433.6
10°	413.3
12.5°	386.0
15°	353.3
17.5°	316.7
20°	277.0
22.5°	237.3
25°	200.3
27.5°	165.9
30°	134.5
32.5°	107.2
35°	83.4
37.5°	63.1
40°	47.2
42.5°	35.3
45°	26.0
47.5°	19.0
50°	14.1
52.5°	11.5
55°	10.1
57.5°	9.3
60°	7.9
62.5°	6.6
65°	5.7
67.5°	4.9
70°	4.4
72.5°	3.5
75°	2.6
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)