

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246197

Luminaire Tested: P3A05R459024DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1246197  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R459024DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R45 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 156.0 lumens  
Efficiency: N/A  
Efficacy: 21.7 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246197

CATALOG NUMBER: P3A05R459024DE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1246197

CATALOG NUMBER: P3A05R459024DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  | 96  | 94  | 93  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  | 89  | 87  | 86  |
| 3   | 102 | 95  | 90  | 86  | 100 | 93  | 89  | 85  | 91  | 87  | 83  |  | 88  | 85  | 82  |  | 86  | 83  | 81  | 79  |
| 4   | 96  | 88  | 83  | 78  | 94  | 87  | 82  | 78  | 85  | 81  | 77  |  | 83  | 79  | 76  |  | 81  | 78  | 75  | 74  |
| 5   | 91  | 83  | 77  | 72  | 90  | 82  | 76  | 72  | 80  | 75  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  | 69  |
| 6   | 87  | 78  | 72  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 66  |  | 74  | 69  | 66  |  | 73  | 69  | 66  | 64  |
| 7   | 83  | 73  | 67  | 63  | 81  | 72  | 67  | 63  | 71  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 65  | 62  | 60  |
| 8   | 79  | 69  | 63  | 59  | 77  | 68  | 63  | 59  | 67  | 62  | 58  |  | 66  | 62  | 58  |  | 65  | 61  | 58  | 56  |
| 9   | 75  | 65  | 59  | 55  | 74  | 65  | 59  | 55  | 64  | 59  | 55  |  | 63  | 58  | 55  |  | 62  | 58  | 55  | 53  |
| 10  | 72  | 62  | 56  | 52  | 71  | 61  | 56  | 52  | 61  | 55  | 52  |  | 60  | 55  | 52  |  | 59  | 55  | 52  | 50  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 46466 |
| 5°  | 45410 |
| 10° | 41883 |
| 15° | 36413 |
| 20° | 29916 |
| 25° | 23276 |
| 30° | 17193 |
| 35° | 12100 |
| 40° | 7557  |
| 45° | 4093  |
| 50° | 2217  |
| 55° | 1912  |
| 60° | 1710  |
| 65° | 1453  |
| 70° | 1218  |
| 75° | 1271  |
| 80° | 1137  |
| 85° | 1006  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 4093 cd/sqm

TEST NUMBER: P1246197

CATALOG NUMBER: P3A05R459024DE010 E3DLP1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 19.1   | 12.2      |
| 10°-20°   | 44.3   | 28.4      |
| 20°-30°   | 44.0   | 28.2      |
| 30°-40°   | 28.4   | 18.2      |
| 40°-50°   | 10.9   | 7.0       |
| 50°-60°   | 4.4    | 2.8       |
| 60°-70°   | 2.8    | 1.8       |
| 70°-80°   | 1.5    | 1.0       |
| 80°-90°   | 0.4    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 107.5  | 68.9      |
| 0°-40°    | 135.8  | 87.1      |
| 0°-60°    | 151.2  | 97.0      |
| 0°-90°    | 156.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 156.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 212 |      |
| 5°  | 206 | 19   |
| 15° | 160 | 44   |
| 25° | 96  | 44   |
| 35° | 45  | 28   |
| 45° | 13  | 11   |
| 55° | 5   | 4    |
| 65° | 3   | 3    |
| 75° | 2   | 2    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1246197

CATALOG NUMBER: P3A05R459024DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 211.9 |
| 2.5°  | 210.8 |
| 5°    | 206.3 |
| 7.5°  | 198.5 |
| 10°   | 188.1 |
| 12.5° | 175.1 |
| 15°   | 160.4 |
| 17.5° | 144.4 |
| 20°   | 128.2 |
| 22.5° | 111.8 |
| 25°   | 96.2  |
| 27.5° | 81.5  |
| 30°   | 67.9  |
| 32.5° | 56.0  |
| 35°   | 45.2  |
| 37.5° | 35.5  |
| 40°   | 26.4  |
| 42.5° | 19.0  |
| 45°   | 13.2  |
| 47.5° | 8.9   |
| 50°   | 6.5   |
| 52.5° | 5.4   |
| 55°   | 5.0   |
| 57.5° | 4.3   |
| 60°   | 3.9   |
| 62.5° | 3.2   |
| 65°   | 2.8   |
| 67.5° | 2.4   |
| 70°   | 1.9   |
| 72.5° | 1.7   |
| 75°   | 1.5   |
| 77.5° | 1.1   |
| 80°   | 0.9   |
| 82.5° | 0.6   |
| 85°   | 0.4   |
| 87.5° | 0.2   |
| 90°   | 0.0   |

(END OF REPORT)