

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302090

Luminaire Tested: P3AS17R60W2N902750DE010 E3DLD1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902750DE010 E3DLD1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 984.0 lumens
Efficiency: N/A
Efficacy: 50.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302090
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLD1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302090
 CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLD1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98 | 99 | 97 | 95 | 95 | 94 | 93 | 91 |
| 2 | 105 | 99 | 94 | 90 | 103 | 97 | 93 | 89 | 94 | 90 | 87 | 91 | 88 | 85 | 88 | 86 | 84 | 82 |
| 3 | 99 | 91 | 85 | 80 | 96 | 89 | 84 | 79 | 87 | 82 | 78 | 84 | 80 | 77 | 82 | 78 | 76 | 74 |
| 4 | 92 | 83 | 77 | 72 | 90 | 82 | 76 | 71 | 80 | 75 | 70 | 78 | 73 | 70 | 76 | 72 | 69 | 67 |
| 5 | 87 | 77 | 70 | 65 | 85 | 76 | 69 | 65 | 74 | 68 | 64 | 72 | 67 | 63 | 71 | 66 | 63 | 61 |
| 6 | 82 | 71 | 64 | 59 | 80 | 70 | 64 | 59 | 69 | 63 | 58 | 67 | 62 | 58 | 66 | 61 | 58 | 56 |
| 7 | 77 | 66 | 59 | 54 | 75 | 65 | 59 | 54 | 64 | 58 | 54 | 63 | 57 | 53 | 61 | 57 | 53 | 51 |
| 8 | 72 | 61 | 55 | 50 | 71 | 61 | 54 | 50 | 60 | 54 | 49 | 59 | 53 | 49 | 58 | 53 | 49 | 47 |
| 9 | 68 | 57 | 51 | 46 | 67 | 57 | 50 | 46 | 56 | 50 | 46 | 55 | 49 | 46 | 54 | 49 | 45 | 44 |
| 10 | 65 | 54 | 47 | 43 | 64 | 53 | 47 | 43 | 52 | 47 | 43 | 52 | 46 | 42 | 51 | 46 | 42 | 41 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 174679 |
| 5° | 172705 |
| 10° | 166730 |
| 15° | 157526 |
| 20° | 145193 |
| 25° | 131475 |
| 30° | 116727 |
| 35° | 99742 |
| 40° | 79320 |
| 45° | 55913 |
| 50° | 33398 |
| 55° | 16898 |
| 60° | 16227 |
| 65° | 14891 |
| 70° | 13784 |
| 75° | 13132 |
| 80° | 12123 |
| 85° | 9057 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 55913 cd/sqm



TEST NUMBER: P1302090

CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLD1WH_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 73.7 | 7.5 |
| 10°-20° | 193.9 | 19.7 |
| 20°-30° | 249.0 | 25.3 |
| 30°-40° | 230.8 | 23.5 |
| 40°-50° | 140.5 | 14.3 |
| 50°-60° | 46.8 | 4.8 |
| 60°-70° | 28.5 | 2.9 |
| 70°-80° | 16.0 | 1.6 |
| 80°-90° | 4.6 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 516.6 | 52.5 |
| 0°-40° | 747.5 | 76.0 |
| 0°-60° | 934.9 | 95.0 |
| 0°-90° | 984.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 984.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 797 | |
| 5° | 785 | 74 |
| 15° | 694 | 194 |
| 25° | 543 | 249 |
| 35° | 373 | 231 |
| 45° | 180 | 141 |
| 55° | 44 | 47 |
| 65° | 29 | 29 |
| 75° | 16 | 16 |
| 85° | 4 | 5 |
| 90° | 0 | |



TEST NUMBER: P1302090
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLD1WH_3000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 796.6 |
| 2.5° | 793.0 |
| 5° | 784.6 |
| 7.5° | 769.1 |
| 10° | 748.8 |
| 12.5° | 723.7 |
| 15° | 693.9 |
| 17.5° | 659.2 |
| 20° | 622.2 |
| 22.5° | 582.8 |
| 25° | 543.4 |
| 27.5° | 502.8 |
| 30° | 461.0 |
| 32.5° | 419.2 |
| 35° | 372.6 |
| 37.5° | 323.6 |
| 40° | 277.1 |
| 42.5° | 228.1 |
| 45° | 180.3 |
| 47.5° | 139.7 |
| 50° | 97.9 |
| 52.5° | 58.5 |
| 55° | 44.2 |
| 57.5° | 40.6 |
| 60° | 37.0 |
| 62.5° | 32.2 |
| 65° | 28.7 |
| 67.5° | 25.1 |
| 70° | 21.5 |
| 72.5° | 17.9 |
| 75° | 15.5 |
| 77.5° | 11.9 |
| 80° | 9.6 |
| 82.5° | 6.0 |
| 85° | 3.6 |
| 87.5° | 2.4 |
| 90° | 0.0 |

(END OF REPORT)