

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246219

Luminaire Tested: P3A05R509024DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R509024DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 497.0 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246219

CATALOG NUMBER: P3A05R509024DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246219

CATALOG NUMBER: P3A05R509024DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	97	92	88		101	95	91	87		93	89	86		90	87	84		88	85	83
4	98	91	85	81		96	90	85	81		87	83	80		85	82	79		84	80	78
5	93	85	80	75		92	84	79	75		83	78	74		81	77	74		79	76	73
6	89	80	75	71		88	80	74	70		78	73	70		77	73	69		75	72	69
7	85	76	70	66		84	75	70	66		74	69	66		73	69	65		72	68	65
8	81	72	66	62		80	71	66	62		70	65	62		69	65	62		68	64	61
9	78	68	63	59		76	68	62	59		67	62	59		66	62	58		65	61	58
10	74	65	59	56		73	65	59	56		64	59	55		63	58	55		62	58	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158233
5°	155051
10°	145221
15°	130012
20°	109396
25°	83497
30°	54262
35°	32177
40°	18606
45°	9303
50°	3480
55°	2714
60°	2500
65°	2283
70°	2244
75°	2288
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9303 cd/sqm

TEST NUMBER: P1246219

CATALOG NUMBER: P3A05R509024DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.5	13.2
10°-20°	158.4	31.9
20°-30°	155.4	31.3
30°-40°	78.3	15.8
40°-50°	24.7	5.0
50°-60°	6.4	1.3
60°-70°	4.5	0.9
70°-80°	2.8	0.6
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.3	76.3
0°-40°	457.6	92.1
0°-60°	488.7	98.3
0°-90°	497.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	497.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	722	
5°	704	66
15°	573	158
25°	345	155
35°	120	78
45°	30	25
55°	7	6
65°	4	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1246219

CATALOG NUMBER: P3A05R509024DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	721.6
2.5°	717.2
5°	704.4
7.5°	681.4
10°	652.2
12.5°	614.7
15°	572.7
17.5°	524.1
20°	468.8
22.5°	409.2
25°	345.1
27.5°	277.1
30°	214.3
32.5°	161.3
35°	120.2
37.5°	88.8
40°	65.0
42.5°	46.0
45°	30.0
47.5°	17.2
50°	10.2
52.5°	7.5
55°	7.1
57.5°	6.2
60°	5.7
62.5°	5.3
65°	4.4
67.5°	4.0
70°	3.5
72.5°	3.1
75°	2.7
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)