

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302105

Luminaire Tested: P3AS17R60W2N902750DE010 E3DLP1H_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902750DE010 E3DLP1H_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 868.0 lumens
Efficiency: N/A
Efficacy: 44.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302105
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1H_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302105
 CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1H_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219982
5°	215034
10°	201332
15°	180614
20°	155320
25°	128427
30°	101484
35°	75355
40°	51897
45°	32562
50°	17910
55°	10475
60°	9429
65°	8042
70°	6860
75°	7032
80°	6061
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 32562 cd/sqm



TEST NUMBER: P1302105

CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1H_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	10.5
10°-20°	221.0	25.5
20°-30°	242.4	27.9
30°-40°	176.6	20.3
40°-50°	83.4	9.6
50°-60°	27.3	3.1
60°-70°	15.5	1.8
70°-80°	8.3	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.3	63.9
0°-40°	730.9	84.2
0°-60°	841.6	97.0
0°-90°	868.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	868.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1003	
5°	977	91
15°	796	221
25°	531	242
35°	282	177
45°	105	83
55°	27	27
65°	16	15
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1302105
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1H_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1003.2
2.5°	997.2
5°	976.9
7.5°	945.9
10°	904.2
12.5°	854.1
15°	795.6
17.5°	732.4
20°	665.6
22.5°	597.6
25°	530.8
27.5°	464.0
30°	400.8
32.5°	340.0
35°	281.5
37.5°	229.0
40°	181.3
42.5°	139.6
45°	105.0
47.5°	76.3
50°	52.5
52.5°	34.6
55°	27.4
57.5°	23.9
60°	21.5
62.5°	17.9
65°	15.5
67.5°	13.1
70°	10.7
72.5°	9.5
75°	8.3
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)