

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302236

Luminaire Tested: P3AS17R60W2N902765DE010 E3DLD1GPH\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302236  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R60W2N902765DE010 E3DLD1GPH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 6500K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 487.1 lumens  
Efficiency: N/A  
Efficacy: 25.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302236  
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DLD1GPH\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1302236

CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DLD1GPH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	86440
5°	85472
10°	82519
15°	77957
20°	71850
25°	65060
30°	57781
35°	49362
40°	39245
45°	27693
50°	16545
55°	8372
60°	8026
65°	7368
70°	6796
75°	6524
80°	5935
85°	4529

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 27693 cd/sqm



TEST NUMBER: P1302236

CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DLD1GPH\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	36.5	7.5
10°-20°	96.0	19.7
20°-30°	123.2	25.3
30°-40°	114.3	23.5
40°-50°	69.6	14.3
50°-60°	23.2	4.8
60°-70°	14.1	2.9
70°-80°	8.0	1.6
80°-90°	2.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.7	52.5
0°-40°	369.9	76.0
0°-60°	462.7	95.0
0°-90°	487.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	487.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	394	
5°	388	36
15°	343	96
25°	269	123
35°	184	114
45°	89	70
55°	22	23
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1302236  
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DLD1GPH\_6500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	394.2
2.5°	392.5
5°	388.3
7.5°	380.6
10°	370.6
12.5°	358.2
15°	343.4
17.5°	326.3
20°	307.9
22.5°	288.4
25°	268.9
27.5°	248.8
30°	228.2
32.5°	207.5
35°	184.4
37.5°	160.2
40°	137.1
42.5°	112.9
45°	89.3
47.5°	69.2
50°	48.5
52.5°	29.0
55°	21.9
57.5°	20.1
60°	18.3
62.5°	16.0
65°	14.2
67.5°	12.4
70°	10.6
72.5°	8.9
75°	7.7
77.5°	5.9
80°	4.7
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)