

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302257

Luminaire Tested: P3AS17R60W2N902765DE010 E3DLD1WH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302257  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R60W2N902765DE010 E3DLD1WH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3500K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 999.0 lumens  
Efficiency: N/A  
Efficacy: 51.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302257  
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DLD1WH\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1302257  
 CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DLD1WH\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98  | 99  | 97  | 95  | 95  | 94  | 93  | 91  |
| 2   | 105 | 99  | 94  | 90  | 103 | 97  | 93  | 89  | 94  | 90  | 87  | 91  | 88  | 85  | 88  | 86  | 84  | 82  |
| 3   | 99  | 91  | 85  | 80  | 96  | 89  | 84  | 79  | 87  | 82  | 78  | 84  | 80  | 77  | 82  | 78  | 76  | 74  |
| 4   | 92  | 83  | 77  | 72  | 90  | 82  | 76  | 71  | 80  | 75  | 70  | 78  | 73  | 70  | 76  | 72  | 69  | 67  |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 69  | 65  | 74  | 68  | 64  | 72  | 67  | 63  | 71  | 66  | 63  | 61  |
| 6   | 82  | 71  | 64  | 59  | 80  | 70  | 64  | 59  | 69  | 63  | 58  | 67  | 62  | 58  | 66  | 61  | 58  | 56  |
| 7   | 77  | 66  | 59  | 54  | 75  | 65  | 59  | 54  | 64  | 58  | 54  | 63  | 57  | 53  | 61  | 57  | 53  | 51  |
| 8   | 72  | 61  | 55  | 50  | 71  | 61  | 54  | 50  | 60  | 54  | 49  | 59  | 53  | 49  | 58  | 53  | 49  | 47  |
| 9   | 68  | 57  | 51  | 46  | 67  | 57  | 50  | 46  | 56  | 50  | 46  | 55  | 49  | 46  | 54  | 49  | 45  | 44  |
| 10  | 65  | 54  | 47  | 43  | 64  | 53  | 47  | 43  | 52  | 47  | 43  | 52  | 46  | 42  | 51  | 46  | 42  | 41  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 177332 |
| 5°  | 175346 |
| 10° | 169269 |
| 15° | 159910 |
| 20° | 147409 |
| 25° | 133484 |
| 30° | 118499 |
| 35° | 101268 |
| 40° | 80522  |
| 45° | 56781  |
| 50° | 33909  |
| 55° | 17165  |
| 60° | 16490  |
| 65° | 15099  |
| 70° | 13977  |
| 75° | 13386  |
| 80° | 12249  |
| 85° | 9057   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 56781 cd/sqm



TEST NUMBER: P1302257

CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DLD1WH\_3500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 74.9   | 7.5       |
| 10°-20°   | 196.9  | 19.7      |
| 20°-30°   | 252.8  | 25.3      |
| 30°-40°   | 234.4  | 23.5      |
| 40°-50°   | 142.7  | 14.3      |
| 50°-60°   | 47.6   | 4.8       |
| 60°-70°   | 28.9   | 2.9       |
| 70°-80°   | 16.3   | 1.6       |
| 80°-90°   | 4.6    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 524.5  | 52.5      |
| 0°-40°    | 758.9  | 76.0      |
| 0°-60°    | 949.2  | 95.0      |
| 0°-90°    | 999.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 999.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 809 |      |
| 5°  | 797 | 75   |
| 15° | 704 | 197  |
| 25° | 552 | 253  |
| 35° | 378 | 234  |
| 45° | 183 | 143  |
| 55° | 45  | 48   |
| 65° | 29  | 29   |
| 75° | 16  | 16   |
| 85° | 4   | 5    |
| 90° | 0   |      |



TEST NUMBER: P1302257  
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DLD1WH\_3500K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 808.7 |
| 2.5°  | 805.1 |
| 5°    | 796.6 |
| 7.5°  | 780.8 |
| 10°   | 760.2 |
| 12.5° | 734.8 |
| 15°   | 704.4 |
| 17.5° | 669.3 |
| 20°   | 631.7 |
| 22.5° | 591.7 |
| 25°   | 551.7 |
| 27.5° | 510.5 |
| 30°   | 468.0 |
| 32.5° | 425.6 |
| 35°   | 378.3 |
| 37.5° | 328.6 |
| 40°   | 281.3 |
| 42.5° | 231.6 |
| 45°   | 183.1 |
| 47.5° | 141.9 |
| 50°   | 99.4  |
| 52.5° | 59.4  |
| 55°   | 44.9  |
| 57.5° | 41.2  |
| 60°   | 37.6  |
| 62.5° | 32.7  |
| 65°   | 29.1  |
| 67.5° | 25.5  |
| 70°   | 21.8  |
| 72.5° | 18.2  |
| 75°   | 15.8  |
| 77.5° | 12.1  |
| 80°   | 9.7   |
| 82.5° | 6.1   |
| 85°   | 3.6   |
| 87.5° | 2.4   |
| 90°   | 0.0   |

(END OF REPORT)