

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302303

Luminaire Tested: P3AS17R65W2N902750DE010 E3CB1MB\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302303  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R65W2N902750DE010 E3CB1MB\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,  
E3CB1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1339.0 lumens  
Efficiency: N/A  
Efficacy: 69.0 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302303  
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MB\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1302303

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MB\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87				87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81				81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75				75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70				70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66				66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62				62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58				58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54				54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51				51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	327233
5°	307968
10°	304069
15°	298685
20°	282008
25°	261741
30°	203449
35°	117704
40°	47432
45°	21832
50°	8494
55°	3326
60°	2851
65°	2802
70°	2757
75°	2711
80°	2778
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21832 cd/sqm



TEST NUMBER: P1302303

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MB\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	133.0	9.9
10°-20°	367.4	27.4
20°-30°	481.0	35.9
30°-40°	278.6	20.8
40°-50°	59.6	4.5
50°-60°	9.7	0.7
60°-70°	5.3	0.4
70°-80°	3.1	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	981.4	73.3
0°-40°	1260.0	94.1
0°-60°	1329.3	99.3
0°-90°	1339.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1339.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1492	
5°	1399	133
15°	1316	367
25°	1082	481
35°	440	279
45°	70	60
55°	9	10
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1302303

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MB\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1492.3
2.5°	1450.0
5°	1399.1
7.5°	1378.5
10°	1365.6
12.5°	1347.1
15°	1315.7
17.5°	1267.0
20°	1208.5
22.5°	1153.3
25°	1081.8
27.5°	961.6
30°	803.5
32.5°	622.7
35°	439.7
37.5°	278.3
40°	165.7
42.5°	104.0
45°	70.4
47.5°	45.5
50°	24.9
52.5°	11.9
55°	8.7
57.5°	7.6
60°	6.5
62.5°	6.5
65°	5.4
67.5°	4.3
70°	4.3
72.5°	3.2
75°	3.2
77.5°	2.2
80°	2.2
82.5°	1.1
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)