

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246438

Luminaire Tested: P3A09R259024DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R259024DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 821.9 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246438
CATALOG NUMBER: P3A09R259024DE010 E3CD1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1246438
 CATALOG NUMBER: P3A09R259024DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	85	85	85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	83	83	83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	81	81	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	79	79	79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	878833
5°	815098
10°	632119
15°	316960
20°	104122
25°	41398
30°	15547
35°	4497
40°	2032
45°	806
50°	648
55°	497
60°	570
65°	675
70°	385
75°	508
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 806 cd/sqm

TEST NUMBER: P1246438
 CATALOG NUMBER: P3A09R259024DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	325.7	39.6
10°-20°	388.6	47.3
20°-30°	87.6	10.7
30°-40°	14.2	1.7
40°-50°	2.6	0.3
50°-60°	1.4	0.2
60°-70°	1.2	0.1
70°-80°	0.6	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	801.9	97.6
0°-40°	816.1	99.3
0°-60°	820.0	99.8
0°-90°	821.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	821.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4008	
5°	3703	326
15°	1396	389
25°	171	88
35°	17	14
45°	3	3
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1246438
CATALOG NUMBER: P3A09R259024DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	4007.8
1°	4001.4
2°	3969.1
3°	3909.7
4°	3819.9
5°	3703.0
6°	3563.5
7°	3412.4
8°	3239.3
9°	3050.1
10°	2838.9
11°	2595.5
12°	2315.2
13°	2022.0
14°	1707.5
15°	1396.2
17.5°	795.6
20°	446.2
22.5°	269.3
25°	171.1
27.5°	105.3
30°	61.4
32.5°	32.3
35°	16.8
37.5°	11.0
40°	7.1
42.5°	4.5
45°	2.6
47.5°	1.9
50°	1.9
52.5°	1.9
55°	1.3
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	1.3
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1246438
CATALOG NUMBER: P3A09R259024DE010 E3CD1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)