

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302309

Luminaire Tested: P3AS17R65W2N902750DE010 E3CB1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302309
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902750DE010 E3CB1MMS_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1477.1 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302309
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MMS_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302309
 CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81		
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75		
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70		
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	360936
5°	339709
10°	335398
15°	329468
20°	311084
25°	288718
30°	224414
35°	129831
40°	52327
45°	24065
50°	9381
55°	3670
60°	3158
65°	3113
70°	3077
75°	3050
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24065 cd/sqm



TEST NUMBER: P1302309

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.7	9.9
10°-20°	405.3	27.4
20°-30°	530.5	35.9
30°-40°	307.3	20.8
40°-50°	65.8	4.5
50°-60°	10.7	0.7
60°-70°	5.9	0.4
70°-80°	3.5	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1082.5	73.3
0°-40°	1389.8	94.1
0°-60°	1466.3	99.3
0°-90°	1477.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1477.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1646	
5°	1543	147
15°	1451	405
25°	1193	531
35°	485	307
45°	78	66
55°	10	11
65°	6	6
75°	4	3
85°	1	1
90°	0	



TEST NUMBER: P1302309
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MMS_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1646.0
2.5°	1599.5
5°	1543.3
7.5°	1520.6
10°	1506.3
12.5°	1486.0
15°	1451.3
17.5°	1397.6
20°	1333.1
22.5°	1272.2
25°	1193.3
27.5°	1060.7
30°	886.3
32.5°	686.8
35°	485.0
37.5°	307.0
40°	182.8
42.5°	114.7
45°	77.6
47.5°	50.2
50°	27.5
52.5°	13.1
55°	9.6
57.5°	8.4
60°	7.2
62.5°	7.2
65°	6.0
67.5°	4.8
70°	4.8
72.5°	3.6
75°	3.6
77.5°	2.4
80°	2.4
82.5°	1.2
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)