

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302342

Luminaire Tested: P3AS17R65W2N902750DE010 E3D1LI_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302342
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902750DE010 E3D1LI_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 90CRI ,
E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1438.1 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302342
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3D1LI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302342

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3D1LI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	385320
5°	357780
10°	345997
15°	333441
20°	308260
25°	280855
30°	216995
35°	125789
40°	49922
45°	21274
50°	5049
55°	688
60°	526
65°	311
70°	385
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21274 cd/sqm



TEST NUMBER: P1302342

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3D1LI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.3	10.7
10°-20°	409.3	28.5
20°-30°	518.0	36.0
30°-40°	295.0	20.5
40°-50°	58.6	4.1
50°-60°	3.1	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1080.5	75.1
0°-40°	1375.5	95.6
0°-60°	1437.2	99.9
0°-90°	1438.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1438.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1757	
5°	1625	153
15°	1469	409
25°	1161	518
35°	470	295
45°	69	59
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1302342

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3D1LI_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1757.2
1°	1744.2
2°	1715.8
3°	1682.7
4°	1650.2
5°	1625.4
6°	1607.1
7°	1592.3
8°	1579.3
9°	1566.3
10°	1553.9
11°	1540.3
12°	1526.1
13°	1509.0
14°	1490.6
15°	1468.8
16°	1442.8
17°	1414.4
18°	1383.7
19°	1351.2
20°	1321.0
21°	1290.3
22°	1262.5
23°	1233.5
24°	1199.8
25°	1160.8
26°	1114.1
27°	1058.0
28°	994.7
29°	927.4
30°	857.0
31°	779.6
32°	702.8
32.5°	663.2
33°	624.7
34°	546.7
35°	469.9
36°	399.0
37°	328.6
37.5°	292.6
38°	263.6
39°	213.4
40°	174.4
42.5°	107.6
45°	68.6



TEST NUMBER: P1302342

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3D1LI_5000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	40.2
50°	14.8
52.5°	3.0
55°	1.8
57.5°	1.2
60°	1.2
62.5°	1.2
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)