

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246473

Luminaire Tested: P3A09R309024DE010 E3D1B

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246473
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R309024DE010 E3D1B
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3D1B TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 815.0 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246473

CATALOG NUMBER: P3A09R309024DE010 E3D1B

Luminous Intensity Polar Plot



TEST NUMBER: P1246473

CATALOG NUMBER: P3A09R309024DE010 E3D1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	87	86	85
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	84	83	82
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	81	80	79
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	79	78	77
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	77	76	75
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	75	74	73
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	73	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	648435
5°	639972
10°	558774
15°	355167
20°	140712
25°	47011
30°	21877
35°	9905
40°	3807
45°	1861
50°	546
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1861 cd/sqm

TEST NUMBER: P1246473

CATALOG NUMBER: P3A09R309024DE010 E3D1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.8	32.6
10°-20°	412.2	50.6
20°-30°	106.3	13.0
30°-40°	25.0	3.1
40°-50°	4.9	0.6
50°-60°	0.5	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	784.3	96.2
0°-40°	809.3	99.3
0°-60°	814.7	100.0
0°-90°	815.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	815.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2957	
5°	2907	266
15°	1564	412
25°	194	106
35°	37	25
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1246473

CATALOG NUMBER: P3A09R309024DE010 E3D1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	2957.1
1°	2954.9
2°	2947.9
3°	2940.0
4°	2928.3
5°	2907.4
6°	2873.6
7°	2817.3
8°	2740.4
9°	2640.1
10°	2509.5
11°	2354.1
12°	2184.5
13°	1989.3
14°	1785.0
15°	1564.5
16°	1348.4
17°	1140.2
18°	940.6
19°	757.4
20°	603.0
21°	474.6
22°	373.3
23°	295.5
24°	236.6
25°	194.3
26°	162.0
27°	137.6
28°	119.0
29°	101.9
30°	86.4
32.5°	54.4
35°	37.0
37.5°	23.1
40°	13.3
42.5°	8.9
45°	6.0
47.5°	3.5
50°	1.6
52.5°	0.6
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3

TEST NUMBER: P1246473

CATALOG NUMBER: P3A09R309024DE010 E3D1B

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)