

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246494

Luminaire Tested: P3A09R309024DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1246494  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R309024DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 683.0 lumens  
Efficiency: N/A  
Efficacy: 61.5 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246494  
CATALOG NUMBER: P3A09R309024DE010 E3DLP1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1246494  
 CATALOG NUMBER: P3A09R309024DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	91	89	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	88	85	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	81	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71	79	75	73	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	76	72	70	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	71	67	65	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	398543
5°	379330
10°	319077
15°	230103
20°	142742
25°	81174
30°	45096
35°	24521
40°	12939
45°	7008
50°	3753
55°	2485
60°	2281
65°	2335
70°	2052
75°	1610
80°	1642
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7008 cd/sqm



TEST NUMBER: P1246494  
 CATALOG NUMBER: P3A09R309024DE010 E3DLP1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.2	22.7
10°-20°	275.8	40.4
20°-30°	159.4	23.3
30°-40°	60.5	8.9
40°-50°	18.6	2.7
50°-60°	6.3	0.9
60°-70°	4.2	0.6
70°-80°	2.3	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	590.4	86.4
0°-40°	651.0	95.3
0°-60°	675.8	98.9
0°-90°	683.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	683.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1818	
5°	1723	155
15°	1014	276
25°	336	159
35°	92	61
45°	23	19
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1246494  
CATALOG NUMBER: P3A09R309024DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1817.5
1°	1816.3
2°	1805.3
3°	1784.6
4°	1758.8
5°	1723.3
6°	1678.2
7°	1627.9
8°	1571.7
9°	1504.6
10°	1433.0
11°	1355.6
12°	1273.6
13°	1187.8
14°	1100.7
15°	1013.6
17.5°	799.4
20°	611.7
22.5°	453.6
25°	335.5
27.5°	243.9
30°	178.1
32.5°	128.4
35°	91.6
37.5°	63.9
40°	45.2
42.5°	31.6
45°	22.6
47.5°	15.5
50°	11.0
52.5°	7.7
55°	6.5
57.5°	5.8
60°	5.2
62.5°	4.5
65°	4.5
67.5°	3.9
70°	3.2
72.5°	2.6
75°	1.9
77.5°	1.9
80°	1.3
82.5°	1.3
85°	0.6
87.5°	0.0



TEST NUMBER: P1246494  
CATALOG NUMBER: P3A09R309024DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)