

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302411

Luminaire Tested: P3AS17R65W2N902750DE010 E3DLD1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302411
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902750DE010 E3DLD1WH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 955.0 lumens
Efficiency: N/A
Efficacy: 49.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302411
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3DLD1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302411
 CATALOG NUMBER: P3AS17R65W2N902750DE010 E3DLD1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169943
5°	167664
10°	162032
15°	152805
20°	140946
25°	127943
30°	113309
35°	96423
40°	76715
45°	54176
50°	31453
55°	17165
60°	15964
65°	14476
70°	13207
75°	12370
80°	10734
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 54176 cd/sqm



TEST NUMBER: P1302411

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3DLD1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.6	7.5
10°-20°	188.3	19.7
20°-30°	242.0	25.3
30°-40°	223.9	23.4
40°-50°	135.2	14.2
50°-60°	46.1	4.8
60°-70°	27.7	2.9
70°-80°	15.7	1.6
80°-90°	4.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	502.0	52.6
0°-40°	725.9	76.0
0°-60°	907.1	95.0
0°-90°	955.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	955.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	775	
5°	762	72
15°	673	188
25°	529	242
35°	360	224
45°	175	135
55°	45	46
65°	28	28
75°	15	16
85°	4	4
90°	0	



TEST NUMBER: P1302411
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3DLD1WH_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	775.0
2.5°	771.4
5°	761.7
7.5°	747.1
10°	727.7
12.5°	703.5
15°	673.1
17.5°	640.4
20°	604.0
22.5°	566.4
25°	528.8
27.5°	488.8
30°	447.5
32.5°	406.3
35°	360.2
37.5°	315.3
40°	268.0
42.5°	220.7
45°	174.7
47.5°	132.2
50°	92.2
52.5°	58.2
55°	44.9
57.5°	40.0
60°	36.4
62.5°	31.5
65°	27.9
67.5°	24.3
70°	20.6
72.5°	18.2
75°	14.6
77.5°	12.1
80°	8.5
82.5°	6.1
85°	3.6
87.5°	2.4
90°	0.0

(END OF REPORT)