

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302502

Luminaire Tested: P3AS17R65W2N902765DE010 E3D1WH_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902765DE010 E3D1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1291.0 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302502
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3D1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1302502
 CATALOG NUMBER: P3AS17R65W2N902765DE010 E3D1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	345937
5°	321197
10°	310615
15°	299343
20°	276757
25°	252160
30°	194815
35°	112939
40°	44798
45°	19103
50°	4537
55°	612
60°	482
65°	259
70°	321
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19103 cd/sqm



TEST NUMBER: P1302502

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3D1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.6	10.7
10°-20°	367.4	28.5
20°-30°	465.0	36.0
30°-40°	264.8	20.5
40°-50°	52.6	4.1
50°-60°	2.8	0.2
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	970.1	75.1
0°-40°	1234.9	95.6
0°-60°	1290.3	99.9
0°-90°	1291.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1291.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1578	
5°	1459	138
15°	1319	367
25°	1042	465
35°	422	265
45°	62	53
55°	2	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1302502
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3D1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1577.6
1°	1565.9
2°	1540.4
3°	1510.7
4°	1481.5
5°	1459.2
6°	1442.8
7°	1429.5
8°	1417.9
9°	1406.2
10°	1395.0
11°	1382.8
12°	1370.1
13°	1354.7
14°	1338.3
15°	1318.6
16°	1295.3
17°	1269.8
18°	1242.2
19°	1213.0
20°	1186.0
21°	1158.4
22°	1133.4
23°	1107.4
24°	1077.2
25°	1042.2
26°	1000.2
27°	949.8
28°	893.1
29°	832.6
30°	769.4
31°	699.9
32°	630.9
32.5°	595.4
33°	560.9
34°	490.8
35°	421.9
36°	358.2
37°	295.0
37.5°	262.7
38°	236.7
39°	191.6
40°	156.5
42.5°	96.6
45°	61.6



TEST NUMBER: P1302502
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3D1WH_2700K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	36.1
50°	13.3
52.5°	2.7
55°	1.6
57.5°	1.1
60°	1.1
62.5°	1.1
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)