

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246587

Luminaire Tested: P3A09R509024DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R509024DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 897.0 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246587

CATALOG NUMBER: P3A09R509024DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1246587

CATALOG NUMBER: P3A09R509024DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	313462
5°	305128
10°	291177
15°	263588
20°	228056
25°	187051
30°	107460
35°	33381
40°	8960
45°	3132
50°	751
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3132 cd/sqm

TEST NUMBER: P1246587

CATALOG NUMBER: P3A09R509024DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.8	14.5
10°-20°	321.7	35.9
20°-30°	338.2	37.7
30°-40°	96.8	10.8
40°-50°	9.4	1.1
50°-60°	0.7	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	789.7	88.0
0°-40°	886.5	98.8
0°-60°	896.7	100.0
0°-90°	897.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	897.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1430	
5°	1386	130
15°	1161	322
25°	773	338
35°	125	97
45°	10	9
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1246587

CATALOG NUMBER: P3A09R509024DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1429.5
1°	1427.3
2°	1421.0
3°	1411.8
4°	1399.5
5°	1386.2
6°	1371.9
7°	1356.7
8°	1342.5
9°	1326.0
10°	1307.7
11°	1286.5
12°	1262.1
13°	1231.7
14°	1198.8
15°	1161.1
16°	1121.3
17°	1082.7
18°	1043.1
19°	1008.3
20°	977.3
21°	947.5
22°	913.7
23°	874.7
24°	829.2
25°	773.1
26°	712.4
27°	644.7
28°	577.3
29°	504.5
30°	424.4
31°	349.4
32°	280.4
32.5°	250.3
33°	220.0
34°	168.7
35°	124.7
36°	91.5
37°	68.0
37.5°	58.9
38°	51.0
39°	39.6
40°	31.3
42.5°	17.7
45°	10.1

TEST NUMBER: P1246587

CATALOG NUMBER: P3A09R509024DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	5.7
50°	2.2
52.5°	0.9
55°	0.6
57.5°	0.6
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)