

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302528

Luminaire Tested: P3AS17R65W2N902765DE010 E3DL1LI_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902765DE010 E3DL1LI_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1216.0 lumens
Efficiency: N/A
Efficacy: 62.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302528
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DL1LI_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1302528

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DL1LI_3500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 120.8 | 9.9 |
| 10°-20° | 313.0 | 25.7 |
| 20°-30° | 365.8 | 30.1 |
| 30°-40° | 255.7 | 21.0 |
| 40°-50° | 112.5 | 9.3 |
| 50°-60° | 25.0 | 2.1 |
| 60°-70° | 12.7 | 1.0 |
| 70°-80° | 7.7 | 0.6 |
| 80°-90° | 2.6 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 799.7 | 65.8 |
| 0°-40° | 1055.4 | 86.8 |
| 0°-60° | 1193.0 | 98.1 |
| 0°-90° | 1216.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1216.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1308 | |
| 5° | 1287 | 121 |
| 15° | 1125 | 313 |
| 25° | 806 | 366 |
| 35° | 406 | 256 |
| 45° | 142 | 113 |
| 55° | 21 | 25 |
| 65° | 13 | 13 |
| 75° | 7 | 8 |
| 85° | 2 | 3 |
| 90° | 0 | |



TEST NUMBER: P1302528
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DL1LI_3500K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1307.8 |
| 2.5° | 1302.9 |
| 5° | 1287.2 |
| 7.5° | 1260.5 |
| 10° | 1224.1 |
| 12.5° | 1179.3 |
| 15° | 1124.8 |
| 17.5° | 1058.1 |
| 20° | 984.2 |
| 22.5° | 900.5 |
| 25° | 806.0 |
| 27.5° | 706.6 |
| 30° | 602.4 |
| 32.5° | 501.8 |
| 35° | 406.0 |
| 37.5° | 322.4 |
| 40° | 248.5 |
| 42.5° | 187.9 |
| 45° | 141.8 |
| 47.5° | 104.2 |
| 50° | 65.4 |
| 52.5° | 33.9 |
| 55° | 20.6 |
| 57.5° | 18.2 |
| 60° | 15.8 |
| 62.5° | 14.5 |
| 65° | 13.3 |
| 67.5° | 10.9 |
| 70° | 9.7 |
| 72.5° | 8.5 |
| 75° | 7.3 |
| 77.5° | 6.1 |
| 80° | 4.8 |
| 82.5° | 3.6 |
| 85° | 2.4 |
| 87.5° | 1.2 |
| 90° | 0.0 |

(END OF REPORT)