

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246598

Luminaire Tested: P3A09R509024DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1246598  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R509024DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 277.0 lumens  
Efficiency: N/A  
Efficacy: 25.0 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246598  
CATALOG NUMBER: P3A09R509024DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1246598

CATALOG NUMBER: P3A09R509024DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83				83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69				69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63				63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58				58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53				53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50				50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46				46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43				43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	56289
5°	55470
10°	53016
15°	49081
20°	44127
25°	38784
30°	32992
35°	26742
40°	20095
45°	12932
50°	6141
55°	4817
60°	4561
65°	4255
70°	3847
75°	3474
80°	3157
85°	3271

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12932 cd/sqm



TEST NUMBER: P1246598  
 CATALOG NUMBER: P3A09R509024DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	23.6	8.5
10°-20°	60.3	21.8
20°-30°	73.3	26.4
30°-40°	62.1	22.4
40°-50°	32.3	11.6
50°-60°	11.6	4.2
60°-70°	8.1	2.9
70°-80°	4.4	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	157.2	56.7
0°-40°	219.3	79.2
0°-60°	263.2	95.0
0°-90°	277.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	277.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	257	
5°	252	24
15°	216	60
25°	160	73
35°	100	62
45°	42	32
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1246598  
CATALOG NUMBER: P3A09R509024DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	256.7
2.5°	255.8
5°	252.0
7.5°	246.3
10°	238.1
12.5°	227.6
15°	216.2
17.5°	203.3
20°	189.1
22.5°	174.5
25°	160.3
27.5°	145.4
30°	130.3
32.5°	115.1
35°	99.9
37.5°	85.0
40°	70.2
42.5°	56.0
45°	41.7
47.5°	27.8
50°	18.0
52.5°	13.9
55°	12.6
57.5°	11.4
60°	10.4
62.5°	9.2
65°	8.2
67.5°	7.0
70°	6.0
72.5°	5.1
75°	4.1
77.5°	3.2
80°	2.5
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)