

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302555

Luminaire Tested: P3AS17R65W2N902765DE010 E3DLD1GPH\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302555  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R65W2N902765DE010 E3DLD1GPH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 6500K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 465.0 lumens  
Efficiency: N/A  
Efficacy: 24.0 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302555  
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLD1GPH\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1302555  
 CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLD1GPH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	82757
5°	81642
10°	78890
15°	74416
20°	68629
25°	62302
30°	55173
35°	46953
40°	37356
45°	26359
50°	15317
55°	8372
60°	7763
65°	7057
70°	6411
75°	6015
80°	5177
85°	4529

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 26359 cd/sqm



TEST NUMBER: P1302555  
 CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLD1GPH\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	34.9	7.5
10°-20°	91.7	19.7
20°-30°	117.8	25.3
30°-40°	109.0	23.4
40°-50°	65.8	14.2
50°-60°	22.5	4.8
60°-70°	13.5	2.9
70°-80°	7.6	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	244.4	52.6
0°-40°	353.4	76.0
0°-60°	441.7	95.0
0°-90°	465.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	465.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	377	
5°	371	35
15°	328	92
25°	258	118
35°	175	109
45°	85	66
55°	22	22
65°	14	14
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1302555  
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLD1GPH\_6500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	377.4
2.5°	375.6
5°	370.9
7.5°	363.8
10°	354.3
12.5°	342.5
15°	327.8
17.5°	311.8
20°	294.1
22.5°	275.8
25°	257.5
27.5°	238.0
30°	217.9
32.5°	197.8
35°	175.4
37.5°	153.5
40°	130.5
42.5°	107.5
45°	85.0
47.5°	64.4
50°	44.9
52.5°	28.3
55°	21.9
57.5°	19.5
60°	17.7
62.5°	15.4
65°	13.6
67.5°	11.8
70°	10.0
72.5°	8.9
75°	7.1
77.5°	5.9
80°	4.1
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)