

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246614

Luminaire Tested: P3A09R559024DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R559024DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 859.0 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246614

CATALOG NUMBER: P3A09R559024DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1246614

CATALOG NUMBER: P3A09R559024DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102			100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96			94
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90			89
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85			84
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	86	83	80			79
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76			74
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72			70
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68			66
8	83	74	69	65	82	74	69	65	73	68	65	72	67	64	71	67	64			63
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61			60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58			57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	238248
5°	236033
10°	245509
15°	242113
20°	223249
25°	181656
30°	110346
35°	38200
40°	10906
45°	5210
50°	2217
55°	994
60°	1140
65°	986
70°	833
75°	1101
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5210 cd/sqm

TEST NUMBER: P1246614

CATALOG NUMBER: P3A09R559024DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.7	12.1
10°-20°	296.4	34.5
20°-30°	330.4	38.5
30°-40°	108.1	12.6
40°-50°	14.2	1.7
50°-60°	3.0	0.4
60°-70°	1.7	0.2
70°-80°	1.1	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	730.5	85.0
0°-40°	838.6	97.6
0°-60°	855.9	99.6
0°-90°	859.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	859.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1086	
5°	1072	104
15°	1066	296
25°	751	330
35°	143	108
45°	17	14
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1246614

CATALOG NUMBER: P3A09R559024DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1086.5
2.5°	1078.8
5°	1072.3
7.5°	1087.8
10°	1102.6
12.5°	1094.9
15°	1066.5
17.5°	1021.3
20°	956.7
22.5°	867.6
25°	750.8
27.5°	602.3
30°	435.8
32.5°	267.3
35°	142.7
37.5°	72.3
40°	38.1
42.5°	24.5
45°	16.8
47.5°	11.6
50°	6.5
52.5°	3.9
55°	2.6
57.5°	2.6
60°	2.6
62.5°	1.9
65°	1.9
67.5°	1.3
70°	1.3
72.5°	1.3
75°	1.3
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)