

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302628

Luminaire Tested: P3AS17R70W2N902750DE010 E3CB1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302628
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R70W2N902750DE010 E3CB1MMS_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1494.1 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302628
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3CB1MMS_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302628

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3CB1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.4	8.1
10°-20°	324.5	21.7
20°-30°	453.3	30.3
30°-40°	420.3	28.1
40°-50°	150.7	10.1
50°-60°	12.8	0.9
60°-70°	6.4	0.4
70°-80°	4.1	0.3
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	898.2	60.1
0°-40°	1318.5	88.2
0°-60°	1482.0	99.2
0°-90°	1494.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1494.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1353	
5°	1286	120
15°	1155	324
25°	988	453
35°	697	420
45°	180	151
55°	10	13
65°	6	6
75°	4	4
85°	1	2
90°	0	



TEST NUMBER: P1302628
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3CB1MMS_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1352.9
2.5°	1332.6
5°	1286.0
7.5°	1243.1
10°	1209.6
12.5°	1182.2
15°	1154.7
17.5°	1121.3
20°	1081.9
22.5°	1036.5
25°	987.5
27.5°	937.4
30°	877.7
32.5°	801.2
35°	697.4
37.5°	564.8
40°	420.3
42.5°	286.6
45°	180.3
47.5°	100.3
50°	43.0
52.5°	14.3
55°	9.6
57.5°	8.4
60°	8.4
62.5°	7.2
65°	6.0
67.5°	6.0
70°	4.8
72.5°	4.8
75°	3.6
77.5°	3.6
80°	2.4
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)