

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246650

Luminaire Tested: P3A09R609024DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1246650  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R609024DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 333.0 lumens  
Efficiency: N/A  
Efficacy: 30.0 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246650  
CATALOG NUMBER: P3A09R609024DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1246650  
 CATALOG NUMBER: P3A09R609024DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73				73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48				48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	78634
5°	77878
10°	75617
15°	70852
20°	62702
25°	52455
30°	41120
35°	29821
40°	19837
45°	12373
50°	6686
55°	1950
60°	1798
65°	1660
70°	1603
75°	1610
80°	1642
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12373 cd/sqm



TEST NUMBER: P1246650  
 CATALOG NUMBER: P3A09R609024DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.3	10.0
10°-20°	86.6	26.0
20°-30°	98.7	29.6
30°-40°	70.0	21.0
40°-50°	31.8	9.5
50°-60°	6.7	2.0
60°-70°	3.2	1.0
70°-80°	2.0	0.6
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	218.6	65.6
0°-40°	288.6	86.7
0°-60°	327.1	98.2
0°-90°	333.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	333.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	359	
5°	354	33
15°	312	87
25°	217	99
35°	111	70
45°	40	32
55°	5	7
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1246650  
CATALOG NUMBER: P3A09R609024DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	358.6
2.5°	357.3
5°	353.8
7.5°	347.8
10°	339.6
12.5°	327.9
15°	312.1
17.5°	292.1
20°	268.7
22.5°	243.4
25°	216.8
27.5°	189.6
30°	162.4
32.5°	136.4
35°	111.4
37.5°	89.3
40°	69.3
42.5°	52.5
45°	39.9
47.5°	29.8
50°	19.6
52.5°	9.2
55°	5.1
57.5°	4.4
60°	4.1
62.5°	3.8
65°	3.2
67.5°	2.8
70°	2.5
72.5°	2.2
75°	1.9
77.5°	1.6
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)