

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302678

Luminaire Tested: P3AS17R70W2N902750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R70W2N902750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 589.0 lumens
Efficiency: N/A
Efficacy: 30.4 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302678
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302678
 CATALOG NUMBER: P3AS17R70W2N902750DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114026
5°	112657
10°	109395
15°	104768
20°	98149
25°	89158
30°	77025
35°	61382
40°	44712
45°	29398
50°	13782
55°	4244
60°	4122
65°	3943
70°	3719
75°	3982
80°	3662
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29398 cd/sqm



TEST NUMBER: P1302678

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	8.2
10°-20°	129.2	21.9
20°-30°	167.9	28.5
30°-40°	142.5	24.2
40°-50°	73.5	12.5
50°-60°	14.1	2.4
60°-70°	7.7	1.3
70°-80°	4.7	0.8
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	345.2	58.6
0°-40°	487.7	82.8
0°-60°	575.3	97.7
0°-90°	589.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	589.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	520	
5°	512	48
15°	462	129
25°	368	168
35°	229	142
45°	95	73
55°	11	14
65°	8	8
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1302678
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	520.0
2.5°	518.2
5°	511.8
7.5°	502.4
10°	491.3
12.5°	477.3
15°	461.5
17.5°	442.2
20°	420.6
22.5°	396.0
25°	368.5
27.5°	337.5
30°	304.2
32.5°	267.3
35°	229.3
37.5°	191.9
40°	156.2
42.5°	122.8
45°	94.8
47.5°	69.6
50°	40.4
52.5°	17.5
55°	11.1
57.5°	10.5
60°	9.4
62.5°	8.8
65°	7.6
67.5°	7.0
70°	5.8
72.5°	5.3
75°	4.7
77.5°	3.5
80°	2.9
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)