

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246691

Luminaire Tested: P3A09R659024DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1246691  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R659024DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 219.0 lumens  
Efficiency: N/A  
Efficacy: 19.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246691

CATALOG NUMBER: P3A09R659024DE010 E3DLP1GPH

### Luminous Intensity Polar Plot



TEST NUMBER: P1246691

CATALOG NUMBER: P3A09R659024DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 30  |     |     |     |     | 10  |     |     |  |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 |  |  | 100 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98  | 97  | 96  | 95  | 94  |  |  | 92  |
| 2   | 107 | 101 | 97  | 93  | 104 | 100 | 96  | 92  | 96  | 93  | 90  | 93  | 91  | 88  | 90  | 88  | 86  |  |  | 85  |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 85  | 82  | 87  | 84  | 81  | 85  | 82  | 79  |  |  | 78  |
| 4   | 95  | 87  | 81  | 77  | 93  | 86  | 80  | 76  | 84  | 79  | 75  | 82  | 78  | 74  | 80  | 76  | 73  |  |  | 72  |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  | 77  | 72  | 69  | 75  | 71  | 68  |  |  | 66  |
| 6   | 85  | 76  | 69  | 65  | 84  | 75  | 69  | 65  | 73  | 68  | 64  | 72  | 67  | 64  | 71  | 66  | 63  |  |  | 62  |
| 7   | 81  | 71  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  | 68  | 63  | 59  | 67  | 62  | 59  |  |  | 57  |
| 8   | 77  | 67  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 59  | 56  | 64  | 59  | 55  | 63  | 58  | 55  |  |  | 54  |
| 9   | 73  | 63  | 57  | 52  | 72  | 62  | 56  | 52  | 61  | 56  | 52  | 60  | 55  | 52  | 59  | 55  | 52  |  |  | 50  |
| 10  | 69  | 59  | 53  | 49  | 68  | 59  | 53  | 49  | 58  | 53  | 49  | 57  | 52  | 49  | 56  | 52  | 49  |  |  | 47  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 55675 |
| 5°  | 54281 |
| 10° | 50545 |
| 15° | 45312 |
| 20° | 39133 |
| 25° | 32542 |
| 30° | 25675 |
| 35° | 19006 |
| 40° | 13110 |
| 45° | 8125  |
| 50° | 4401  |
| 55° | 2791  |
| 60° | 2368  |
| 65° | 2127  |
| 70° | 1795  |
| 75° | 1610  |
| 80° | 1642  |
| 85° | 1510  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8125 cd/sqm

TEST NUMBER: P1246691

CATALOG NUMBER: P3A09R659024DE010 E3DLP1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 22.9   | 10.5      |
| 10°-20°   | 55.5   | 25.3      |
| 20°-30°   | 61.3   | 28.0      |
| 30°-40°   | 44.5   | 20.3      |
| 40°-50°   | 20.8   | 9.5       |
| 50°-60°   | 7.0    | 3.2       |
| 60°-70°   | 4.1    | 1.9       |
| 70°-80°   | 2.1    | 1.0       |
| 80°-90°   | 0.7    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 139.7  | 63.8      |
| 0°-40°    | 184.3  | 84.1      |
| 0°-60°    | 212.1  | 96.9      |
| 0°-90°    | 219.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 219.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 254 |      |
| 5°  | 247 | 23   |
| 15° | 200 | 55   |
| 25° | 134 | 61   |
| 35° | 71  | 45   |
| 45° | 26  | 21   |
| 55° | 7   | 7    |
| 65° | 4   | 4    |
| 75° | 2   | 2    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1246691

CATALOG NUMBER: P3A09R659024DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 253.9 |
| 2.5°  | 252.3 |
| 5°    | 246.6 |
| 7.5°  | 238.1 |
| 10°   | 227.0 |
| 12.5° | 214.1 |
| 15°   | 199.6 |
| 17.5° | 183.8 |
| 20°   | 167.7 |
| 22.5° | 150.9 |
| 25°   | 134.5 |
| 27.5° | 117.8 |
| 30°   | 101.4 |
| 32.5° | 85.6  |
| 35°   | 71.0  |
| 37.5° | 57.8  |
| 40°   | 45.8  |
| 42.5° | 35.0  |
| 45°   | 26.2  |
| 47.5° | 18.9  |
| 50°   | 12.9  |
| 52.5° | 8.8   |
| 55°   | 7.3   |
| 57.5° | 6.3   |
| 60°   | 5.4   |
| 62.5° | 4.7   |
| 65°   | 4.1   |
| 67.5° | 3.5   |
| 70°   | 2.8   |
| 72.5° | 2.5   |
| 75°   | 1.9   |
| 77.5° | 1.6   |
| 80°   | 1.3   |
| 82.5° | 0.9   |
| 85°   | 0.6   |
| 87.5° | 0.3   |
| 90°   | 0.0   |

(END OF REPORT)