

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302725

Luminaire Tested: P3AS17R70W2N902750DE010 E3DLP1MW\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302725  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R70W2N902750DE010 E3DLP1MW\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 90CRI ,  
E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 871.0 lumens  
Efficiency: N/A  
Efficacy: 44.9 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302725  
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3DLP1MW\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1302725  
 CATALOG NUMBER: P3AS17R70W2N902750DE010 E3DLP1MW\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77	77	77	77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71	71	71	71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65	65	65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	204304
5°	200550
10°	189108
15°	171624
20°	150116
25°	126636
30°	103687
35°	80442
40°	57565
45°	36438
50°	18183
55°	11125
60°	9561
65°	8821
70°	7758
75°	7202
80°	6061
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 36438 cd/sqm



TEST NUMBER: P1302725

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3DLP1MW\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	85.0	9.8
10°-20°	210.4	24.2
20°-30°	239.6	27.5
30°-40°	187.4	21.5
40°-50°	92.0	10.6
50°-60°	28.3	3.2
60°-70°	16.8	1.9
70°-80°	9.0	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.0	61.4
0°-40°	722.3	82.9
0°-60°	842.6	96.7
0°-90°	871.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	871.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	932	
5°	911	85
15°	756	210
25°	523	240
35°	300	187
45°	118	92
55°	29	28
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1302725  
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3DLP1MW\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	931.7
2.5°	926.8
5°	911.1
7.5°	885.7
10°	849.3
12.5°	806.9
15°	756.0
17.5°	701.5
20°	643.3
22.5°	582.8
25°	523.4
27.5°	465.2
30°	409.5
32.5°	353.8
35°	300.5
37.5°	249.6
40°	201.1
42.5°	156.3
45°	117.5
47.5°	82.4
50°	53.3
52.5°	35.1
55°	29.1
57.5°	25.4
60°	21.8
62.5°	19.4
65°	17.0
67.5°	14.5
70°	12.1
72.5°	9.7
75°	8.5
77.5°	7.3
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)