

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246835

Luminaire Tested: P3A13R209024DE010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1246835  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R209024DE010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 887.0 lumens  
Efficiency: N/A  
Efficacy: 60.8 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246835  
CATALOG NUMBER: P3A13R209024DE010 E3DL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1246835

CATALOG NUMBER: P3A13R209024DE010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71	71	71	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68	68	68	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66	66	66	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	682445
5°	620359
10°	458486
15°	283611
20°	161971
25°	92473
30°	51856
35°	28215
40°	15458
45°	8497
50°	4981
55°	3594
60°	3377
65°	3113
70°	2757
75°	2881
80°	2147
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8497 cd/sqm



TEST NUMBER: P1246835  
 CATALOG NUMBER: P3A13R209024DE010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	244.0	27.5
10°-20°	348.4	39.3
20°-30°	181.8	20.5
30°-40°	70.3	7.9
40°-50°	22.8	2.6
50°-60°	9.0	1.0
60°-70°	5.9	0.7
70°-80°	3.5	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	774.3	87.3
0°-40°	844.6	95.2
0°-60°	876.4	98.8
0°-90°	887.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	887.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3112	
5°	2818	244
15°	1249	348
25°	382	182
35°	105	70
45°	27	23
55°	9	9
65°	6	6
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1246835  
CATALOG NUMBER: P3A13R209024DE010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3112.2
1°	3106.2
2°	3069.4
3°	3012.8
4°	2925.4
5°	2818.3
6°	2691.5
7°	2550.9
8°	2388.1
9°	2229.6
10°	2059.1
12.5°	1636.6
15°	1249.3
17.5°	934.9
20°	694.1
22.5°	514.1
25°	382.2
27.5°	281.9
30°	204.8
32.5°	148.2
35°	105.4
37.5°	76.3
40°	54.0
42.5°	38.6
45°	27.4
47.5°	19.7
50°	14.6
52.5°	11.1
55°	9.4
57.5°	8.6
60°	7.7
62.5°	6.9
65°	6.0
67.5°	5.1
70°	4.3
72.5°	4.3
75°	3.4
77.5°	2.6
80°	1.7
82.5°	1.7
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)