

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246899

Luminaire Tested: P3A13R309024DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R309024DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 698.0 lumens
Efficiency: N/A
Efficacy: 47.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246899
CATALOG NUMBER: P3A13R309024DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1246899

CATALOG NUMBER: P3A13R309024DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			76
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	164899
5°	161193
10°	149897
15°	133395
20°	114717
25°	97191
30°	80671
35°	63282
40°	45371
45°	29740
50°	16955
55°	11125
60°	10525
65°	9755
70°	8784
75°	7964
80°	7577
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29740 cd/sqm



TEST NUMBER: P1246899
 CATALOG NUMBER: P3A13R309024DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.0	9.7
10°-20°	163.3	23.4
20°-30°	184.1	26.4
30°-40°	147.0	21.1
40°-50°	75.6	10.8
50°-60°	28.4	4.1
60°-70°	18.6	2.7
70°-80°	10.0	1.4
80°-90°	2.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	415.4	59.5
0°-40°	562.4	80.6
0°-60°	666.4	95.5
0°-90°	698.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	698.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	752	
5°	732	68
15°	588	163
25°	402	184
35°	236	147
45°	96	76
55°	29	28
65°	19	19
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P1246899
CATALOG NUMBER: P3A13R309024DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	752.0
1°	752.0
2°	749.5
3°	745.2
4°	739.2
5°	732.3
6°	723.8
7°	712.6
8°	700.6
9°	686.9
10°	673.2
11°	657.8
12°	641.5
13°	624.4
14°	606.4
15°	587.6
17.5°	539.6
20°	491.6
22.5°	445.4
25°	401.7
27.5°	358.9
30°	318.6
32.5°	277.5
35°	236.4
37.5°	196.1
40°	158.5
42.5°	125.1
45°	95.9
47.5°	71.1
50°	49.7
52.5°	35.1
55°	29.1
57.5°	26.6
60°	24.0
62.5°	21.4
65°	18.8
67.5°	16.3
70°	13.7
72.5°	11.1
75°	9.4
77.5°	7.7
80°	6.0
82.5°	4.3
85°	2.6
87.5°	0.9



TEST NUMBER: P1246899
CATALOG NUMBER: P3A13R309024DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)