

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246991

Luminaire Tested: P3A13R459024DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246991
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R459024DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 2400K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 618.0 lumens
Efficiency: N/A
Efficacy: 42.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246991
CATALOG NUMBER: P3A13R459024DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1246991
 CATALOG NUMBER: P3A13R459024DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64				64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60				60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56				56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	184086
5°	179881
10°	165929
15°	144291
20°	118544
25°	92231
30°	68112
35°	47917
40°	29913
45°	16219
50°	8767
55°	7531
60°	6754
65°	5759
70°	4937
75°	5083
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16219 cd/sqm



TEST NUMBER: P1246991
 CATALOG NUMBER: P3A13R459024DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.7	12.2
10°-20°	175.7	28.4
20°-30°	174.4	28.2
30°-40°	112.3	18.2
40°-50°	43.3	7.0
50°-60°	17.6	2.8
60°-70°	11.1	1.8
70°-80°	6.0	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.8	68.9
0°-40°	538.2	87.1
0°-60°	599.0	96.9
0°-90°	618.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	618.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	840	
5°	817	76
15°	636	176
25°	381	174
35°	179	112
45°	52	43
55°	20	18
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1246991
CATALOG NUMBER: P3A13R459024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	839.5
2.5°	835.2
5°	817.2
7.5°	786.4
10°	745.2
12.5°	693.8
15°	635.6
17.5°	572.2
20°	508.0
22.5°	442.9
25°	381.2
27.5°	322.9
30°	269.0
32.5°	221.9
35°	179.0
37.5°	140.5
40°	104.5
42.5°	75.4
45°	52.3
47.5°	35.1
50°	25.7
52.5°	21.4
55°	19.7
57.5°	17.1
60°	15.4
62.5°	12.8
65°	11.1
67.5°	9.4
70°	7.7
72.5°	6.9
75°	6.0
77.5°	4.3
80°	3.4
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)