

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247080

Luminaire Tested: P3A13R659024DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247080
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R659024DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1060.0 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247080

CATALOG NUMBER: P3A13R659024DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1247080

CATALOG NUMBER: P3A13R659024DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		60	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	259036
5°	243803
10°	240699
15°	236460
20°	223249
25°	207206
30°	161063
35°	93184
40°	37556
45°	17273
50°	6720
55°	2638
60°	2237
65°	2231
70°	2180
75°	2203
80°	2147
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17273 cd/sqm

TEST NUMBER: P1247080

CATALOG NUMBER: P3A13R659024DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.3	9.9
10°-20°	290.9	27.4
20°-30°	380.8	35.9
30°-40°	220.5	20.8
40°-50°	47.2	4.5
50°-60°	7.7	0.7
60°-70°	4.2	0.4
70°-80°	2.5	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	776.9	73.3
0°-40°	997.5	94.1
0°-60°	1052.3	99.3
0°-90°	1060.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1060.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1181	
5°	1108	105
15°	1042	291
25°	856	381
35°	348	221
45°	56	47
55°	7	8
65°	4	4
75°	3	2
85°	1	1
90°	0	

TEST NUMBER: P1247080

CATALOG NUMBER: P3A13R659024DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1181.3
2.5°	1147.9
5°	1107.6
7.5°	1091.3
10°	1081.0
12.5°	1066.4
15°	1041.6
17.5°	1003.0
20°	956.7
22.5°	913.0
25°	856.4
27.5°	761.3
30°	636.1
32.5°	492.9
35°	348.1
37.5°	220.3
40°	131.2
42.5°	82.3
45°	55.7
47.5°	36.0
50°	19.7
52.5°	9.4
55°	6.9
57.5°	6.0
60°	5.1
62.5°	5.1
65°	4.3
67.5°	3.4
70°	3.4
72.5°	2.6
75°	2.6
77.5°	1.7
80°	1.7
82.5°	0.9
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)