

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250424

Luminaire Tested: P3A24R509027D010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250424
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24R509027D010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2473.9 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250424
CATALOG NUMBER: P3A24R509027D010 E3CB1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1250424
 CATALOG NUMBER: P3A24R509027D010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 | 102 | 101 | 99 | 98 | 97 | 97 | 95 | 95 | 95 | 95 |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 97 | 95 | 97 | 95 | 93 | 94 | 93 | 91 | 90 | 90 | 90 | 90 |
| 3 | 105 | 99 | 95 | 91 | 103 | 98 | 94 | 90 | 95 | 92 | 89 | 93 | 90 | 88 | 91 | 88 | 86 | 85 | 85 | 85 | 85 |
| 4 | 100 | 94 | 89 | 85 | 99 | 92 | 88 | 85 | 90 | 87 | 84 | 88 | 85 | 83 | 87 | 84 | 82 | 80 | 80 | 80 | 80 |
| 5 | 96 | 89 | 84 | 80 | 94 | 88 | 83 | 79 | 86 | 82 | 79 | 84 | 81 | 78 | 83 | 80 | 77 | 76 | 76 | 76 | 76 |
| 6 | 92 | 84 | 79 | 75 | 91 | 83 | 79 | 75 | 82 | 78 | 74 | 81 | 77 | 74 | 79 | 76 | 73 | 72 | 72 | 72 | 72 |
| 7 | 88 | 80 | 75 | 71 | 87 | 79 | 74 | 71 | 78 | 74 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 69 | 69 | 69 | 69 |
| 8 | 85 | 76 | 71 | 67 | 83 | 76 | 71 | 67 | 75 | 70 | 67 | 74 | 70 | 67 | 73 | 69 | 66 | 65 | 65 | 65 | 65 |
| 9 | 81 | 73 | 68 | 64 | 80 | 72 | 67 | 64 | 71 | 67 | 64 | 71 | 66 | 63 | 70 | 66 | 63 | 62 | 62 | 62 | 62 |
| 10 | 78 | 69 | 64 | 61 | 77 | 69 | 64 | 61 | 68 | 64 | 61 | 68 | 63 | 61 | 67 | 63 | 60 | 59 | 59 | 59 | 59 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 861620 |
| 5° | 846201 |
| 10° | 812499 |
| 15° | 745067 |
| 20° | 656984 |
| 25° | 503569 |
| 30° | 273789 |
| 35° | 88098 |
| 40° | 20696 |
| 45° | 2791 |
| 50° | 2456 |
| 55° | 2753 |
| 60° | 2368 |
| 65° | 2802 |
| 70° | 2308 |
| 75° | 3050 |
| 80° | 2273 |
| 85° | 4529 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 85°
 Luminance: 4529 cd/sqm



TEST NUMBER: P1250424
 CATALOG NUMBER: P3A24R509027D010 E3CB1MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 360.8 | 14.6 |
| 10°-20° | 912.3 | 36.9 |
| 20°-30° | 913.7 | 36.9 |
| 30°-40° | 256.9 | 10.4 |
| 40°-50° | 15.5 | 0.6 |
| 50°-60° | 5.8 | 0.2 |
| 60°-70° | 4.7 | 0.2 |
| 70°-80° | 3.1 | 0.1 |
| 80°-90° | 1.2 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2186.7 | 88.4 |
| 0°-40° | 2443.6 | 98.8 |
| 0°-60° | 2464.9 | 99.6 |
| 0°-90° | 2473.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2473.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3929 | |
| 5° | 3844 | 361 |
| 15° | 3282 | 912 |
| 25° | 2081 | 914 |
| 35° | 329 | 257 |
| 45° | 9 | 15 |
| 55° | 7 | 6 |
| 65° | 5 | 5 |
| 75° | 4 | 3 |
| 85° | 2 | 1 |
| 90° | 0 | |



TEST NUMBER: P1250424
CATALOG NUMBER: P3A24R509027D010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3929.3 |
| 2.5° | 3909.4 |
| 5° | 3844.3 |
| 7.5° | 3755.7 |
| 10° | 3649.0 |
| 12.5° | 3488.1 |
| 15° | 3282.0 |
| 17.5° | 3045.1 |
| 20° | 2815.4 |
| 22.5° | 2529.7 |
| 25° | 2081.3 |
| 27.5° | 1549.7 |
| 30° | 1081.3 |
| 32.5° | 652.8 |
| 35° | 329.1 |
| 37.5° | 155.5 |
| 40° | 72.3 |
| 42.5° | 27.1 |
| 45° | 9.0 |
| 47.5° | 7.2 |
| 50° | 7.2 |
| 52.5° | 7.2 |
| 55° | 7.2 |
| 57.5° | 5.4 |
| 60° | 5.4 |
| 62.5° | 5.4 |
| 65° | 5.4 |
| 67.5° | 3.6 |
| 70° | 3.6 |
| 72.5° | 3.6 |
| 75° | 3.6 |
| 77.5° | 1.8 |
| 80° | 1.8 |
| 82.5° | 1.8 |
| 85° | 1.8 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

IRiS

Report Number: SP1-2508-518-1

Test Date: 09/09/2025

Luminaire Tested: LD3A24R159027D010 E3D1LI

Data in this report applies to families of products including LD3A24R159027D010 E3D1LI


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2508-518-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 09/16/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: IRiS
 Catalog Number: **LD3A24R159027D010 E3D1LI**
 Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3D1LI TRIM

Spectral Parameters

CCT (K): 2737
 CIE u': 0.2605
 CIE v': 0.5285
 Duv: 0.0013
 CIE x: 0.4590
 CIE y: 0.4138
 CIE z: 0.1272
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 583
 Purity: 62.00127
 Rf: 90.8
 Rg: 99.1

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 91.4 | | |
| R1: | 92.1 | R9: | 46.0 |
| R2: | 95.0 | R10: | 87.1 |
| R3: | 97.1 | R11: | 94.9 |
| R4: | 93.2 | R12: | 83.0 |
| R5: | 91.6 | R13: | 92.7 |
| R6: | 95.8 | R14: | 97.1 |
| R7: | 90.2 | R15: | 85.9 |
| R8: | 76.6 | | |



Test Conditions


Stabilization Time: 70M
 Operation Time: 2H 10M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2508-518-1


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | 76INCH SPHERE IN0058 | 6/16/2025 | 12/16/2025 |
| Power Meter | XITRON INXT2011004 | 1/21/2025 | 1/21/2026 |
| AC Power Source | CHROMA 61603 IN0063 | 10/22/2024 | 10/22/2025 |
| DC Power Source | AGILENT E3634A IN0208 | 10/22/2024 | 10/22/2025 |
| Sphere Thermometer | ONSET IN0085 | 10/22/2024 | 10/22/2025 |
| Room Thermometer | ONSET IN0046 | 10/22/2024 | 10/22/2025 |

REPORT NUMBER: SP1-2508-518-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2508-518-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 100 | NR | 620 | 447 | NR | 750 | 16 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 123 | NR | 625 | 443 | NR | 755 | 13 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 148 | NR | 630 | 1000 | NR | 760 | 11 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 173 | NR | 635 | 764 | NR | 765 | 10 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 194 | NR | 640 | 317 | NR | 770 | 9 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 211 | NR | 645 | 298 | NR | 775 | 7 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 224 | NR | 650 | 271 | NR | 780 | 7 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 235 | NR | 655 | 232 | NR | 785 | 6 | NR | 915 | 0 | NR |
| 400 | 1 | NR | 530 | 245 | NR | 660 | 202 | NR | 790 | 5 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 255 | NR | 665 | 175 | NR | 795 | 4 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 265 | NR | 670 | 160 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 8 | NR | 545 | 273 | NR | 675 | 137 | NR | 805 | 3 | NR | 935 | 0 | NR |
| 420 | 15 | NR | 550 | 284 | NR | 680 | 119 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 24 | NR | 555 | 295 | NR | 685 | 104 | NR | 815 | 2 | NR | 945 | 0 | NR |
| 430 | 38 | NR | 560 | 309 | NR | 690 | 91 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 60 | NR | 565 | 321 | NR | 695 | 79 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 88 | NR | 570 | 336 | NR | 700 | 68 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 121 | NR | 575 | 350 | NR | 705 | 59 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 158 | NR | 580 | 367 | NR | 710 | 51 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 161 | NR | 585 | 384 | NR | 715 | 44 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 128 | NR | 590 | 398 | NR | 720 | 38 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 100 | NR | 595 | 407 | NR | 725 | 33 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 83 | NR | 600 | 420 | NR | 730 | 28 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 74 | NR | 605 | 431 | NR | 735 | 24 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 73 | NR | 610 | 486 | NR | 740 | 20 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 82 | NR | 615 | 541 | NR | 745 | 17 | NR | 875 | 1 | NR | | | |

REPORT NUMBER: SP1-2508-518-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.27

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 100 | NR | 620 | 447 | NR | 750 | 16 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 123 | NR | 625 | 443 | NR | 755 | 13 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 148 | NR | 630 | 1000 | NR | 760 | 11 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 173 | NR | 635 | 764 | NR | 765 | 10 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 194 | NR | 640 | 317 | NR | 770 | 9 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 211 | NR | 645 | 298 | NR | 775 | 7 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 224 | NR | 650 | 271 | NR | 780 | 7 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 235 | NR | 655 | 232 | NR | 785 | 6 | NR | 915 | 0 | NR |
| 400 | 1 | NR | 530 | 245 | NR | 660 | 202 | NR | 790 | 5 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 255 | NR | 665 | 175 | NR | 795 | 4 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 265 | NR | 670 | 160 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 8 | NR | 545 | 273 | NR | 675 | 137 | NR | 805 | 3 | NR | 935 | 0 | NR |
| 420 | 15 | NR | 550 | 284 | NR | 680 | 119 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 24 | NR | 555 | 295 | NR | 685 | 104 | NR | 815 | 2 | NR | 945 | 0 | NR |
| 430 | 38 | NR | 560 | 309 | NR | 690 | 91 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 60 | NR | 565 | 321 | NR | 695 | 79 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 88 | NR | 570 | 336 | NR | 700 | 68 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 121 | NR | 575 | 350 | NR | 705 | 59 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 158 | NR | 580 | 367 | NR | 710 | 51 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 161 | NR | 585 | 384 | NR | 715 | 44 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 128 | NR | 590 | 398 | NR | 720 | 38 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 100 | NR | 595 | 407 | NR | 725 | 33 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 83 | NR | 600 | 420 | NR | 730 | 28 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 74 | NR | 605 | 431 | NR | 735 | 24 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 73 | NR | 610 | 486 | NR | 740 | 20 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 82 | NR | 615 | 541 | NR | 745 | 17 | NR | 875 | 1 | NR | | | |

REPORT NUMBER: SP1-2508-518-1

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 2.37





| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 100 | NR | 620 | 447 | NR | 750 | 16 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 123 | NR | 625 | 443 | NR | 755 | 13 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 148 | NR | 630 | 1000 | NR | 760 | 11 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 173 | NR | 635 | 764 | NR | 765 | 10 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 194 | NR | 640 | 317 | NR | 770 | 9 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 211 | NR | 645 | 298 | NR | 775 | 7 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 224 | NR | 650 | 271 | NR | 780 | 7 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 235 | NR | 655 | 232 | NR | 785 | 6 | NR | 915 | 0 | NR |
| 400 | 1 | NR | 530 | 245 | NR | 660 | 202 | NR | 790 | 5 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 255 | NR | 665 | 175 | NR | 795 | 4 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 265 | NR | 670 | 160 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 8 | NR | 545 | 273 | NR | 675 | 137 | NR | 805 | 3 | NR | 935 | 0 | NR |
| 420 | 15 | NR | 550 | 284 | NR | 680 | 119 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 24 | NR | 555 | 295 | NR | 685 | 104 | NR | 815 | 2 | NR | 945 | 0 | NR |
| 430 | 38 | NR | 560 | 309 | NR | 690 | 91 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 60 | NR | 565 | 321 | NR | 695 | 79 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 88 | NR | 570 | 336 | NR | 700 | 68 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 121 | NR | 575 | 350 | NR | 705 | 59 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 158 | NR | 580 | 367 | NR | 710 | 51 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 161 | NR | 585 | 384 | NR | 715 | 44 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 128 | NR | 590 | 398 | NR | 720 | 38 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 100 | NR | 595 | 407 | NR | 725 | 33 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 83 | NR | 600 | 420 | NR | 730 | 28 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 74 | NR | 605 | 431 | NR | 735 | 24 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 73 | NR | 610 | 486 | NR | 740 | 20 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 82 | NR | 615 | 541 | NR | 745 | 17 | NR | 875 | 1 | NR | | | |

Summary

$R_f = 90.8$
 $R_g = 99.1$
 $CIE R_a = 91.4$
 $R_9 = 46.0$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 91 | CES51 = 98 | CES76 = 89 |
| CES02 = 64 | CES27 = 96 | CES52 = 98 | CES77 = 85 |
| CES03 = 32 | CES28 = 96 | CES53 = 95 | CES78 = 87 |
| CES04 = 71 | CES29 = 91 | CES54 = 97 | CES79 = 89 |
| CES05 = 51 | CES30 = 97 | CES55 = 97 | CES80 = 91 |
| CES06 = 51 | CES31 = 92 | CES56 = 94 | CES81 = 70 |
| CES07 = 44 | CES32 = 85 | CES57 = 93 | CES82 = 96 |
| CES08 = 42 | CES33 = 94 | CES58 = 95 | CES83 = 93 |
| CES09 = 29 | CES34 = 94 | CES59 = 97 | CES84 = 96 |
| CES10 = 77 | CES35 = 97 | CES60 = 97 | CES85 = 80 |
| CES11 = 59 | CES36 = 91 | CES61 = 95 | CES86 = 74 |
| CES12 = 66 | CES37 = 94 | CES62 = 95 | CES87 = 92 |
| CES13 = 44 | CES38 = 98 | CES63 = 92 | CES88 = 95 |
| CES14 = 74 | CES39 = 97 | CES64 = 93 | CES89 = 81 |
| CES15 = 72 | CES40 = 95 | CES65 = 88 | CES90 = 96 |
| CES16 = 48 | CES41 = 95 | CES66 = 91 | CES91 = 86 |
| CES17 = 50 | CES42 = 93 | CES67 = 90 | CES92 = 76 |
| CES18 = 57 | CES43 = 93 | CES68 = 92 | CES93 = 85 |
| CES19 = 72 | CES44 = 99 | CES69 = 94 | CES94 = 70 |
| CES20 = 68 | CES45 = 96 | CES70 = 89 | CES95 = 85 |
| CES21 = 87 | CES46 = 94 | CES71 = 88 | CES96 = 91 |
| CES22 = 79 | CES47 = 88 | CES72 = 96 | CES97 = 94 |
| CES23 = 92 | CES48 = 92 | CES73 = 85 | CES98 = 92 |
| CES24 = 91 | CES49 = 93 | CES74 = 89 | CES99 = 89 |
| CES25 = 72 | CES50 = 98 | CES75 = 88 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)