

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247091

Luminaire Tested: P3A13R659024DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247091
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R659024DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 860.0 lumens
Efficiency: N/A
Efficacy: 58.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247091

CATALOG NUMBER: P3A13R659024DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1247091

CATALOG NUMBER: P3A13R659024DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63		
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202813
5°	200374
10°	192782
15°	180591
20°	162414
25°	137911
30°	107865
35°	76881
40°	50294
45°	31104
50°	15795
55°	5582
60°	4868
65°	4877
70°	4424
75°	4321
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31104 cd/sqm

TEST NUMBER: P1247091

CATALOG NUMBER: P3A13R659024DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.5	9.9
10°-20°	221.4	25.7
20°-30°	258.7	30.1
30°-40°	180.8	21.0
40°-50°	79.6	9.3
50°-60°	17.7	2.1
60°-70°	9.0	1.0
70°-80°	5.4	0.6
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.6	65.8
0°-40°	746.4	86.8
0°-60°	843.7	98.1
0°-90°	860.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	860.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	925	
5°	910	85
15°	796	221
25°	570	259
35°	287	181
45°	100	80
55°	15	18
65°	9	9
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1247091

CATALOG NUMBER: P3A13R659024DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	924.9
2.5°	921.5
5°	910.3
7.5°	891.5
10°	865.8
12.5°	834.0
15°	795.5
17.5°	748.3
20°	696.0
22.5°	636.9
25°	570.0
27.5°	499.7
30°	426.0
32.5°	354.9
35°	287.2
37.5°	228.0
40°	175.7
42.5°	132.9
45°	100.3
47.5°	73.7
50°	46.3
52.5°	24.0
55°	14.6
57.5°	12.9
60°	11.1
62.5°	10.3
65°	9.4
67.5°	7.7
70°	6.9
72.5°	6.0
75°	5.1
77.5°	4.3
80°	3.4
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)