

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250475

Luminaire Tested: P3A24R559027D010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250475
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24R559027D010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1315.0 lumens
Efficiency: N/A
Efficacy: 45.7 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250475

CATALOG NUMBER: P3A24R559027D010 E3DLP1H

Luminous Intensity Polar Plot



TEST NUMBER: P1250475

CATALOG NUMBER: P3A24R559027D010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	357713
5°	348755
10°	324220
15°	288719
20°	245348
25°	198011
30°	150960
35°	107371
40°	70847
45°	42020
50°	24664
55°	15177
60°	13464
65°	12193
70°	10450
75°	9150
80°	9092
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42020 cd/sqm

TEST NUMBER: P1250475

CATALOG NUMBER: P3A24R559027D010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.1	11.2
10°-20°	352.6	26.8
20°-30°	373.5	28.4
30°-40°	252.4	19.2
40°-50°	110.6	8.4
50°-60°	39.6	3.0
60°-70°	23.2	1.8
70°-80°	12.1	0.9
80°-90°	3.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	873.2	66.4
0°-40°	1125.5	85.6
0°-60°	1275.7	97.0
0°-90°	1315.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1315.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1631	
5°	1584	147
15°	1272	353
25°	818	373
35°	401	252
45°	136	111
55°	40	40
65°	24	23
75°	11	12
85°	4	4
90°	0	

TEST NUMBER: P1250475

CATALOG NUMBER: P3A24R559027D010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1631.3
2.5°	1618.7
5°	1584.4
7.5°	1528.4
10°	1456.1
12.5°	1369.4
15°	1271.8
17.5°	1163.4
20°	1051.4
22.5°	934.0
25°	818.4
27.5°	704.6
30°	596.2
32.5°	493.2
35°	401.1
37.5°	318.0
40°	247.5
42.5°	186.1
45°	135.5
47.5°	99.4
50°	72.3
52.5°	50.6
55°	39.7
57.5°	36.1
60°	30.7
62.5°	27.1
65°	23.5
67.5°	19.9
70°	16.3
72.5°	14.5
75°	10.8
77.5°	9.0
80°	7.2
82.5°	5.4
85°	3.6
87.5°	1.8
90°	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

IRiS

Report Number: SP1-2508-518-1

Test Date: 09/09/2025

Luminaire Tested: LD3A24R159027D010 E3D1LI

Data in this report applies to families of products including LD3A24R159027D010 E3D1LI


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2508-518-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4 π
 Issue Date: 09/16/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: IRiS
 Catalog Number: **LD3A24R159027D010 E3D1LI**
 Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3D1LI TRIM

Spectral Parameters

CCT (K): 2737
 CIE u': 0.2605
 CIE v': 0.5285
 Duv: 0.0013
 CIE x: 0.4590
 CIE y: 0.4138
 CIE z: 0.1272
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 583
 Purity: 62.00127
 Rf: 90.8
 Rg: 99.1

CRI (Ra): 91.4
 R1: 92.1
 R2: 95.0
 R3: 97.1
 R4: 93.2
 R5: 91.6
 R6: 95.8
 R7: 90.2
 R8: 76.6
 R9: 46.0
 R10: 87.1
 R11: 94.9
 R12: 83.0
 R13: 92.7
 R14: 97.1
 R15: 85.9



Test Conditions


Stabilization Time: 70M
 Operation Time: 2H 10M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2508-518-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2508-518-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2508-518-1





TM-30-18

Summary

$R_f = 90.8$
 $R_g = 99.1$
 $CIE R_a = 91.4$
 $R_9 = 46.0$







Color Vector Graphics





Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 91	CES51 = 98	CES76 = 89
CES02 = 64	CES27 = 96	CES52 = 98	CES77 = 85
CES03 = 32	CES28 = 96	CES53 = 95	CES78 = 87
CES04 = 71	CES29 = 91	CES54 = 97	CES79 = 89
CES05 = 51	CES30 = 97	CES55 = 97	CES80 = 91
CES06 = 51	CES31 = 92	CES56 = 94	CES81 = 70
CES07 = 44	CES32 = 85	CES57 = 93	CES82 = 96
CES08 = 42	CES33 = 94	CES58 = 95	CES83 = 93
CES09 = 29	CES34 = 94	CES59 = 97	CES84 = 96
CES10 = 77	CES35 = 97	CES60 = 97	CES85 = 80
CES11 = 59	CES36 = 91	CES61 = 95	CES86 = 74
CES12 = 66	CES37 = 94	CES62 = 95	CES87 = 92
CES13 = 44	CES38 = 98	CES63 = 92	CES88 = 95
CES14 = 74	CES39 = 97	CES64 = 93	CES89 = 81
CES15 = 72	CES40 = 95	CES65 = 88	CES90 = 96
CES16 = 48	CES41 = 95	CES66 = 91	CES91 = 86
CES17 = 50	CES42 = 93	CES67 = 90	CES92 = 76
CES18 = 57	CES43 = 93	CES68 = 92	CES93 = 85
CES19 = 72	CES44 = 99	CES69 = 94	CES94 = 70
CES20 = 68	CES45 = 96	CES70 = 89	CES95 = 85
CES21 = 87	CES46 = 94	CES71 = 88	CES96 = 91
CES22 = 79	CES47 = 88	CES72 = 96	CES97 = 94
CES23 = 92	CES48 = 92	CES73 = 85	CES98 = 92
CES24 = 91	CES49 = 93	CES74 = 89	CES99 = 89
CES25 = 72	CES50 = 98	CES75 = 88	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)