

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247097

Luminaire Tested: P3A13R659024DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R659024DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 675.0 lumens
Efficiency: N/A
Efficacy: 46.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247097
CATALOG NUMBER: P3A13R659024DE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1247097
 CATALOG NUMBER: P3A13R659024DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120122
5°	118512
10°	114538
15°	108014
20°	99619
25°	90441
30°	80088
35°	68154
40°	54244
45°	38268
50°	22242
55°	12119
60°	11271
65°	10222
70°	9361
75°	8727
80°	7577
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 38268 cd/sqm



TEST NUMBER: P1247097
 CATALOG NUMBER: P3A13R659024DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	7.5
10°-20°	133.1	19.7
20°-30°	171.1	25.3
30°-40°	158.3	23.4
40°-50°	95.5	14.2
50°-60°	32.6	4.8
60°-70°	19.6	2.9
70°-80°	11.1	1.6
80°-90°	3.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	354.8	52.6
0°-40°	513.1	76.0
0°-60°	641.2	95.0
0°-90°	675.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	675.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	548	
5°	538	51
15°	476	133
25°	374	171
35°	255	158
45°	123	96
55°	32	33
65°	20	20
75°	10	11
85°	3	3
90°	0	



TEST NUMBER: P1247097
CATALOG NUMBER: P3A13R659024DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	547.8
2.5°	545.2
5°	538.4
7.5°	528.1
10°	514.4
12.5°	497.2
15°	475.8
17.5°	452.6
20°	426.9
22.5°	400.3
25°	373.8
27.5°	345.5
30°	316.3
32.5°	287.2
35°	254.6
37.5°	222.9
40°	189.5
42.5°	156.0
45°	123.4
47.5°	93.4
50°	65.2
52.5°	41.1
55°	31.7
57.5°	28.3
60°	25.7
62.5°	22.3
65°	19.7
67.5°	17.1
70°	14.6
72.5°	12.9
75°	10.3
77.5°	8.6
80°	6.0
82.5°	4.3
85°	2.6
87.5°	1.7
90°	0.0

(END OF REPORT)