

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247314

Luminaire Tested: P3A17R359024DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247314
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R359024DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 880.0 lumens
Efficiency: N/A
Efficacy: 41.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247314
CATALOG NUMBER: P3A17R359024DE010 E3PHLD1MW

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270°



TEST NUMBER: P1247314
 CATALOG NUMBER: P3A17R359024DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	88		
2	103	96	90	85	100	94	89	84	90	86	82	87	84	81	84	81	79	77		
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68		
4	88	78	71	65	86	77	70	65	75	68	64	72	67	63	70	66	62	60		
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54		
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	55	50	46	44		
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41		
9	64	52	45	40	63	51	44	40	50	44	39	49	44	39	48	43	39	38		
10	60	49	42	37	59	48	41	37	47	41	37	46	41	36	45	40	36	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	144440	144440	144440
5°	141734	141492	141734
10°	133264	133019	133264
15°	120659	120659	120909
20°	106806	106806	106806
25°	92884	92594	92594
30°	80519	79936	80240
35°	69306	69011	69306
40°	60141	59826	60141
45°	52843	52471	52471
50°	46873	46497	46497
55°	41251	41251	41251
60°	37365	36839	37365
65°	33570	33570	33570
70°	29877	29877	29877
75°	26942	26010	26942
80°	22983	22983	22983
85°	14341	14341	14341

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 52843 cd/sqm



TEST NUMBER: P1247314
 CATALOG NUMBER: P3A17R359024DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.9	6.8
10°-20°	148.3	16.8
20°-30°	176.2	20.0
30°-40°	161.9	18.4
40°-50°	131.4	14.9
50°-60°	97.3	11.1
60°-70°	64.2	7.3
70°-80°	33.3	3.8
80°-90°	7.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	384.3	43.7
0°-40°	546.2	62.1
0°-60°	774.9	88.1
0°-90°	880.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	880.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	659	659	659	659	659	
5°	644	643	643	643	644	60
15°	532	532	532	532	533	148
25°	384	383	383	384	383	177
35°	259	258	258	259	259	162
45°	170	169	169	169	169	132
55°	108	108	108	108	108	98
65°	65	65	65	65	65	64
75°	32	32	31	32	32	34
85°	6	6	6	6	6	7
90°	0	0	0	0	0	



TEST NUMBER: P1247314

CATALOG NUMBER: P3A17R359024DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	658.7	658.7	658.7	658.7	658.7
1°	658.7	657.6	657.6	657.6	658.7
2°	656.4	656.4	656.4	656.4	656.4
3°	654.2	653.0	653.0	653.0	653.0
4°	649.6	648.5	648.5	648.5	648.5
5°	643.9	642.8	642.8	642.8	643.9
6°	637.1	636.0	634.9	634.9	636.0
7°	630.3	628.0	628.0	628.0	628.0
8°	620.1	619.0	619.0	619.0	619.0
9°	609.9	607.6	608.7	608.7	608.7
10°	598.5	597.4	597.4	597.4	598.5
11°	587.2	586.0	586.0	584.9	586.0
12°	573.5	573.5	573.5	573.5	573.5
13°	561.0	559.9	559.9	559.9	561.0
14°	547.4	546.3	546.3	546.3	546.3
15°	531.5	531.5	531.5	531.5	532.6
17.5°	495.2	494.0	495.2	495.2	496.3
20°	457.7	456.6	457.7	457.7	457.7
22.5°	420.2	420.2	419.1	420.2	421.3
25°	383.9	382.7	382.7	383.9	382.7
27.5°	349.8	348.7	348.7	348.7	348.7
30°	318.0	315.7	315.7	316.9	316.9
32.5°	285.1	285.1	286.2	285.1	285.1
35°	258.9	257.8	257.8	258.9	258.9
37.5°	232.8	231.7	231.7	232.8	232.8
40°	210.1	210.1	209.0	210.1	210.1
42.5°	188.5	188.5	188.5	188.5	188.5
45°	170.4	169.2	169.2	169.2	169.2
47.5°	152.2	152.2	152.2	151.0	152.2
50°	137.4	136.3	136.3	136.3	136.3
52.5°	121.5	121.5	121.5	121.5	121.5
55°	107.9	107.9	107.9	107.9	107.9
57.5°	96.5	95.4	95.4	95.4	95.4
60°	85.2	85.2	84.0	85.2	85.2
62.5°	73.8	73.8	73.8	73.8	73.8
65°	64.7	64.7	64.7	64.7	64.7
67.5°	55.6	55.6	55.6	55.6	55.6
70°	46.6	46.6	46.6	46.6	46.6
72.5°	39.7	38.6	38.6	38.6	38.6
75°	31.8	31.8	30.7	31.8	31.8
77.5°	23.8	23.8	23.8	23.8	23.8
80°	18.2	18.2	18.2	17.0	18.2
82.5°	11.4	11.4	11.4	11.4	11.4
85°	5.7	5.7	5.7	5.7	5.7
87.5°	1.1	1.1	1.1	2.3	2.3



TEST NUMBER: P1247314
CATALOG NUMBER: P3A17R359024DE010 E3PHLD1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)