

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247435

Luminaire Tested: P3A17R609024DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247435
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R609024DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1361.0 lumens
Efficiency: N/A
Efficacy: 64.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247435
CATALOG NUMBER: P3A17R609024DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1247435
 CATALOG NUMBER: P3A17R609024DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | | | | 94 |
| 2 | 108 | 104 | 100 | 96 | 106 | 102 | 98 | 95 | 99 | 96 | 93 | 96 | 93 | 91 | 93 | 91 | 89 | 88 | | | | 88 |
| 3 | 103 | 97 | 92 | 88 | 101 | 96 | 91 | 88 | 93 | 89 | 86 | 91 | 87 | 85 | 88 | 86 | 84 | 82 | | | | 82 |
| 4 | 98 | 91 | 85 | 81 | 96 | 90 | 85 | 81 | 88 | 83 | 80 | 86 | 82 | 79 | 84 | 81 | 78 | 77 | | | | 77 |
| 5 | 93 | 85 | 80 | 75 | 92 | 84 | 79 | 75 | 83 | 78 | 74 | 81 | 77 | 74 | 79 | 76 | 73 | 72 | | | | 72 |
| 6 | 89 | 80 | 74 | 70 | 87 | 79 | 74 | 70 | 78 | 73 | 70 | 77 | 72 | 69 | 75 | 71 | 69 | 67 | | | | 67 |
| 7 | 85 | 76 | 70 | 66 | 83 | 75 | 69 | 65 | 74 | 69 | 65 | 72 | 68 | 65 | 71 | 67 | 64 | 63 | | | | 63 |
| 8 | 81 | 71 | 65 | 61 | 79 | 71 | 65 | 61 | 70 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 61 | 59 | | | | 59 |
| 9 | 77 | 67 | 62 | 58 | 76 | 67 | 61 | 58 | 66 | 61 | 57 | 65 | 61 | 57 | 64 | 60 | 57 | 56 | | | | 56 |
| 10 | 73 | 64 | 58 | 54 | 72 | 63 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 54 | 61 | 57 | 54 | 53 | | | | 53 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 356594 |
| 5° | 336649 |
| 10° | 327894 |
| 15° | 320388 |
| 20° | 297899 |
| 25° | 266314 |
| 30° | 203424 |
| 35° | 117437 |
| 40° | 45571 |
| 45° | 18979 |
| 50° | 4162 |
| 55° | 650 |
| 60° | 482 |
| 65° | 311 |
| 70° | 385 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18979 cd/sqm



TEST NUMBER: P1247435
 CATALOG NUMBER: P3A17R609024DE010 E3D1LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 144.4 | 10.6 |
| 10°-20° | 393.1 | 28.9 |
| 20°-30° | 492.4 | 36.2 |
| 30°-40° | 275.2 | 20.2 |
| 40°-50° | 52.3 | 3.8 |
| 50°-60° | 2.7 | 0.2 |
| 60°-70° | 0.7 | 0.0 |
| 70°-80° | 0.2 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1029.9 | 75.7 |
| 0°-40° | 1305.2 | 95.9 |
| 0°-60° | 1360.1 | 99.9 |
| 0°-90° | 1361.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1361.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1626 | |
| 5° | 1529 | 144 |
| 15° | 1411 | 393 |
| 25° | 1101 | 492 |
| 35° | 439 | 275 |
| 45° | 61 | 52 |
| 55° | 2 | 3 |
| 65° | 1 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1247435
CATALOG NUMBER: P3A17R609024DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1626.2 |
| 1° | 1619.6 |
| 2° | 1598.4 |
| 3° | 1573.3 |
| 4° | 1550.0 |
| 5° | 1529.4 |
| 6° | 1513.8 |
| 7° | 1500.4 |
| 8° | 1490.4 |
| 9° | 1480.9 |
| 10° | 1472.6 |
| 11° | 1464.2 |
| 12° | 1454.8 |
| 13° | 1443.1 |
| 14° | 1429.1 |
| 15° | 1411.3 |
| 16° | 1389.6 |
| 17° | 1365.1 |
| 18° | 1337.3 |
| 19° | 1305.5 |
| 20° | 1276.6 |
| 21° | 1245.4 |
| 22° | 1213.1 |
| 23° | 1179.2 |
| 24° | 1141.9 |
| 25° | 1100.7 |
| 26° | 1052.2 |
| 27° | 998.2 |
| 28° | 937.5 |
| 29° | 873.0 |
| 30° | 803.4 |
| 31° | 733.2 |
| 32° | 660.8 |
| 32.5° | 621.3 |
| 33° | 585.7 |
| 34° | 511.6 |
| 35° | 438.7 |
| 36° | 373.0 |
| 37° | 303.4 |
| 37.5° | 271.7 |
| 38° | 240.5 |
| 39° | 193.7 |
| 40° | 159.2 |
| 42.5° | 96.9 |
| 45° | 61.2 |



TEST NUMBER: P1247435
CATALOG NUMBER: P3A17R609024DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|------|
| 47.5° | 34.0 |
| 50° | 12.2 |
| 52.5° | 2.8 |
| 55° | 1.7 |
| 57.5° | 1.1 |
| 60° | 1.1 |
| 62.5° | 0.6 |
| 65° | 0.6 |
| 67.5° | 0.6 |
| 70° | 0.6 |
| 72.5° | 0.6 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)