

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247480

Luminaire Tested: P3A17R659024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R659024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 386.0 lumens
Efficiency: N/A
Efficacy: 18.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247480
CATALOG NUMBER: P3A17R659024DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1247480

CATALOG NUMBER: P3A17R659024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98106
5°	95663
10°	89088
15°	79842
20°	68956
25°	57366
30°	45222
35°	33515
40°	23100
45°	14327
50°	7778
55°	4893
60°	4166
65°	3736
70°	3206
75°	2796
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14327 cd/sqm



TEST NUMBER: P1247480
 CATALOG NUMBER: P3A17R659024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.4	10.5
10°-20°	97.7	25.3
20°-30°	108.1	28.0
30°-40°	78.5	20.3
40°-50°	36.8	9.5
50°-60°	12.4	3.2
60°-70°	7.1	1.8
70°-80°	3.7	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	246.2	63.8
0°-40°	324.7	84.1
0°-60°	373.9	96.9
0°-90°	386.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	386.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	447	
5°	435	40
15°	352	98
25°	237	108
35°	125	78
45°	46	37
55°	13	12
65°	7	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1247480
CATALOG NUMBER: P3A17R659024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	447.4
2.5°	444.7
5°	434.6
7.5°	419.6
10°	400.1
12.5°	377.3
15°	351.7
17.5°	323.9
20°	295.5
22.5°	266.0
25°	237.1
27.5°	207.6
30°	178.6
32.5°	150.8
35°	125.2
37.5°	101.8
40°	80.7
42.5°	61.8
45°	46.2
47.5°	33.4
50°	22.8
52.5°	15.6
55°	12.8
57.5°	11.1
60°	9.5
62.5°	8.3
65°	7.2
67.5°	6.1
70°	5.0
72.5°	4.5
75°	3.3
77.5°	2.8
80°	2.2
82.5°	1.7
85°	1.1
87.5°	0.6
90°	0.0

(END OF REPORT)