

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247554

Luminaire Tested: P3A20R209024D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R209024D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 756.0 lumens
Efficiency: N/A
Efficacy: 26.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247554
CATALOG NUMBER: P3A20R209024D010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1247554
 CATALOG NUMBER: P3A20R209024D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71	71	71	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68	68	68	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	581664
5°	528746
10°	390774
15°	241727
20°	138052
25°	78803
30°	44184
35°	24039
40°	13168
45°	7257
50°	4230
55°	3058
60°	2895
65°	2646
70°	2372
75°	2457
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7257 cd/sqm



TEST NUMBER: P1247554
 CATALOG NUMBER: P3A20R209024D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.0	27.5
10°-20°	296.9	39.3
20°-30°	155.0	20.5
30°-40°	59.9	7.9
40°-50°	19.5	2.6
50°-60°	7.6	1.0
60°-70°	5.1	0.7
70°-80°	3.0	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.9	87.3
0°-40°	719.8	95.2
0°-60°	747.0	98.8
0°-90°	756.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	756.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2653	
5°	2402	208
15°	1065	297
25°	326	155
35°	90	60
45°	23	19
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1247554
CATALOG NUMBER: P3A20R209024D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2652.6
1°	2647.5
2°	2616.0
3°	2567.8
4°	2493.4
5°	2402.1
6°	2294.0
7°	2174.2
8°	2035.4
9°	1900.3
10°	1755.0
12.5°	1394.9
15°	1064.8
17.5°	796.8
20°	591.6
22.5°	438.2
25°	325.7
27.5°	240.3
30°	174.5
32.5°	126.3
35°	89.8
37.5°	65.0
40°	46.0
42.5°	32.9
45°	23.4
47.5°	16.8
50°	12.4
52.5°	9.5
55°	8.0
57.5°	7.3
60°	6.6
62.5°	5.8
65°	5.1
67.5°	4.4
70°	3.7
72.5°	3.7
75°	2.9
77.5°	2.2
80°	1.5
82.5°	1.5
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)