

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247635

Luminaire Tested: P3A20R359024D010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247635
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R359024D010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1893.1 lumens
Efficiency: N/A
Efficacy: 65.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247635

CATALOG NUMBER: P3A20R359024D010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1247635

CATALOG NUMBER: P3A20R359024D010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	98	95	105	101	97	95	98	96	93		96	94	92		94
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81
9	89	82	77	74	88	81	77	74	80	77	74		80	76	74		79
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1234353
5°	1209220
10°	1124940
15°	824749
20°	422323
25°	152210
30°	59275
35°	20746
40°	8530
45°	2326
50°	2047
55°	2294
60°	1974
65°	1557
70°	1923
75°	2542
80°	1894
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 2542 cd/sqm

TEST NUMBER: P1247635

CATALOG NUMBER: P3A20R359024D010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.1	27.1
10°-20°	960.9	50.8
20°-30°	340.2	18.0
30°-40°	59.6	3.1
40°-50°	8.7	0.5
50°-60°	4.9	0.3
60°-70°	3.5	0.2
70°-80°	2.6	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1813.2	95.8
0°-40°	1872.8	98.9
0°-60°	1886.4	99.6
0°-90°	1893.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1893.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5629	
5°	5494	512
15°	3633	961
25°	629	340
35°	78	60
45°	8	9
55°	6	5
65°	3	4
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1247635

CATALOG NUMBER: P3A20R359024D010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5629.1
1°	5627.6
2°	5609.8
3°	5575.5
4°	5544.2
5°	5493.5
6°	5441.3
7°	5383.2
8°	5311.6
9°	5199.8
10°	5052.2
11°	4848.0
12°	4602.0
13°	4309.8
14°	3987.8
15°	3633.0
17.5°	2705.7
20°	1809.8
22.5°	1091.2
25°	629.1
27.5°	375.7
30°	234.1
32.5°	135.7
35°	77.5
37.5°	49.2
40°	29.8
42.5°	14.9
45°	7.5
47.5°	6.0
50°	6.0
52.5°	6.0
55°	6.0
57.5°	4.5
60°	4.5
62.5°	4.5
65°	3.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0



TEST NUMBER: P1247635
CATALOG NUMBER: P3A20R359024D010 E3CB1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)