

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247740

Luminaire Tested: P3A20R509024D010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1247740  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R509024D010 E3DLP1LI  
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1101.1 lumens  
Efficiency: N/A  
Efficacy: 38.2 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247740

CATALOG NUMBER: P3A20R509024D010 E3DLP1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1247740

CATALOG NUMBER: P3A20R509024D010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 95  | 94  | 93  |    |    |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  | 94  | 91  | 89  | 91  | 89  | 87  | 85  |    |    |
| 3   | 101 | 95  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 83  | 88  | 85  | 82  | 86  | 83  | 81  | 79  |    |    |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 82  | 78  | 85  | 80  | 77  | 83  | 79  | 76  | 81  | 78  | 75  | 73  |    |    |
| 5   | 91  | 83  | 76  | 72  | 90  | 82  | 76  | 72  | 80  | 75  | 71  | 78  | 74  | 70  | 77  | 73  | 70  | 68  |    |    |
| 6   | 87  | 77  | 71  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 66  | 74  | 69  | 66  | 72  | 68  | 65  | 64  |    |    |
| 7   | 82  | 73  | 67  | 62  | 81  | 72  | 66  | 62  | 71  | 66  | 62  | 70  | 65  | 61  | 68  | 64  | 61  | 60  |    |    |
| 8   | 78  | 69  | 63  | 58  | 77  | 68  | 62  | 58  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 57  | 56  |    |    |
| 9   | 75  | 65  | 59  | 55  | 74  | 64  | 59  | 55  | 63  | 58  | 55  | 63  | 58  | 54  | 62  | 57  | 54  | 53  |    |    |
| 10  | 71  | 61  | 56  | 52  | 70  | 61  | 55  | 52  | 60  | 55  | 51  | 59  | 55  | 51  | 59  | 54  | 51  | 50  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 320216 |
| 5°  | 311599 |
| 10° | 287347 |
| 15° | 252692 |
| 20° | 211418 |
| 25° | 167647 |
| 30° | 123006 |
| 35° | 84564  |
| 40° | 53758  |
| 45° | 30050  |
| 50° | 16272  |
| 55° | 13686  |
| 60° | 11753  |
| 65° | 10844  |
| 70° | 9553   |
| 75° | 8811   |
| 80° | 7577   |
| 85° | 7548   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30050 cd/sqm

TEST NUMBER: P1247740

CATALOG NUMBER: P3A20R509024D010 E3DLP1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 131.1  | 11.9      |
| 10°-20°   | 308.3  | 28.0      |
| 20°-30°   | 315.3  | 28.6      |
| 30°-40°   | 200.0  | 18.2      |
| 40°-50°   | 79.6   | 7.2       |
| 50°-60°   | 32.3   | 2.9       |
| 60°-70°   | 20.6   | 1.9       |
| 70°-80°   | 10.6   | 1.0       |
| 80°-90°   | 3.3    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 754.8  | 68.5      |
| 0°-40°    | 954.7  | 86.7      |
| 0°-60°    | 1066.6 | 96.9      |
| 0°-90°    | 1101.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1101.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1460 |      |
| 5°  | 1416 | 131  |
| 15° | 1113 | 308  |
| 25° | 693  | 315  |
| 35° | 316  | 200  |
| 45° | 97   | 80   |
| 55° | 36   | 32   |
| 65° | 21   | 21   |
| 75° | 10   | 11   |
| 85° | 3    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1247740

CATALOG NUMBER: P3A20R509024D010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1460.3 |
| 2.5°  | 1449.9 |
| 5°    | 1415.6 |
| 7.5°  | 1362.0 |
| 10°   | 1290.5 |
| 12.5° | 1205.5 |
| 15°   | 1113.1 |
| 17.5° | 1011.8 |
| 20°   | 906.0  |
| 22.5° | 800.2  |
| 25°   | 692.9  |
| 27.5° | 585.6  |
| 30°   | 485.8  |
| 32.5° | 396.4  |
| 35°   | 315.9  |
| 37.5° | 247.4  |
| 40°   | 187.8  |
| 42.5° | 138.6  |
| 45°   | 96.9   |
| 47.5° | 65.6   |
| 50°   | 47.7   |
| 52.5° | 40.2   |
| 55°   | 35.8   |
| 57.5° | 31.3   |
| 60°   | 26.8   |
| 62.5° | 23.8   |
| 65°   | 20.9   |
| 67.5° | 17.9   |
| 70°   | 14.9   |
| 72.5° | 11.9   |
| 75°   | 10.4   |
| 77.5° | 7.5    |
| 80°   | 6.0    |
| 82.5° | 4.5    |
| 85°   | 3.0    |
| 87.5° | 1.5    |
| 90°   | 0.0    |

(END OF REPORT)