

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247754

Luminaire Tested: P3A20R559024D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R559024D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1924.0 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247754

CATALOG NUMBER: P3A20R559024D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1247754

CATALOG NUMBER: P3A20R559024D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	98	94	90	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	84	98	92	87	84	90	86	83		88	84	82		86
5	95	88	83	79	94	87	82	78	85	81	78		84	80	77		82
6	91	83	78	74	90	82	77	74	81	76	73		80	76	73		78
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75
8	83	75	69	66	82	74	69	66	73	69	65		72	68	65		71
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68
10	77	68	62	59	76	67	62	59	67	62	59		66	62	59		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	557938
5°	538189
10°	557438
15°	549583
20°	508641
25°	411362
30°	246519
35°	83547
40°	23015
45°	10203
50°	3002
55°	573
60°	307
65°	363
70°	449
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10203 cd/sqm

TEST NUMBER: P1247754

CATALOG NUMBER: P3A20R559024D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.6	12.3
10°-20°	674.0	35.0
20°-30°	749.2	38.9
30°-40°	233.2	12.1
40°-50°	28.0	1.5
50°-60°	2.2	0.1
60°-70°	0.7	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1659.8	86.3
0°-40°	1893.0	98.4
0°-60°	1923.2	100.0
0°-90°	1924.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1924.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2544	
5°	2445	237
15°	2421	674
25°	1700	749
35°	312	233
45°	33	28
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1247754

CATALOG NUMBER: P3A20R559024D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2544.4
1°	2534.9
2°	2510.0
3°	2479.3
4°	2451.6
5°	2445.0
6°	2452.3
7°	2467.7
8°	2485.2
9°	2499.1
10°	2503.5
11°	2500.5
12°	2488.9
13°	2470.6
14°	2449.4
15°	2420.9
16°	2388.0
17°	2346.3
18°	2299.5
19°	2243.3
20°	2179.7
21°	2107.3
22°	2021.8
23°	1927.5
24°	1819.3
25°	1700.2
26°	1569.3
27°	1430.4
28°	1282.1
29°	1129.3
30°	973.6
31°	817.2
32°	664.4
32.5°	596.4
33°	526.3
34°	407.1
35°	312.1
36°	237.6
37°	176.2
37.5°	150.6
38°	130.8
39°	99.4
40°	80.4
42.5°	51.2
45°	32.9



TEST NUMBER: P1247754
CATALOG NUMBER: P3A20R559024D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	19.7
50°	8.8
52.5°	2.9
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)