

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247756

Luminaire Tested: P3A20R559024D010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R559024D010 E3DL1H
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1625.0 lumens
Efficiency: N/A
Efficacy: 56.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247756

CATALOG NUMBER: P3A20R559024D010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1247756

CATALOG NUMBER: P3A20R559024D010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		106	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		86	78	73	68		77	72	68		75	71	68		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	64	60		78	70	64	60		69	63	60		67	63	60		67	62	59
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56
10	73	63	57	53		72	62	57	53		62	57	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	446214
5°	441689
10°	426534
15°	394259
20°	340230
25°	268709
30°	190612
35°	122924
40°	73824
45°	41617
50°	22379
55°	7990
60°	7192
65°	6953
70°	6668
75°	6354
80°	5683
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41617 cd/sqm

TEST NUMBER: P1247756

CATALOG NUMBER: P3A20R559024D010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.7	11.6
10°-20°	480.3	29.6
20°-30°	503.3	31.0
30°-40°	293.6	18.1
40°-50°	109.9	6.8
50°-60°	25.9	1.6
60°-70°	13.3	0.8
70°-80°	7.9	0.5
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1172.3	72.1
0°-40°	1465.9	90.2
0°-60°	1601.6	98.6
0°-90°	1625.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1625.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2035	
5°	2007	189
15°	1737	480
25°	1111	503
35°	459	294
45°	134	110
55°	21	26
65°	13	13
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1247756

CATALOG NUMBER: P3A20R559024D010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2034.9
2.5°	2028.9
5°	2006.6
7.5°	1970.8
10°	1915.6
12.5°	1838.1
15°	1736.7
17.5°	1608.5
20°	1458.0
22.5°	1289.5
25°	1110.6
27.5°	927.3
30°	752.8
32.5°	594.8
35°	459.2
37.5°	348.8
40°	257.9
42.5°	184.9
45°	134.2
47.5°	96.9
50°	65.6
52.5°	37.3
55°	20.9
57.5°	17.9
60°	16.4
62.5°	14.9
65°	13.4
67.5°	11.9
70°	10.4
72.5°	8.9
75°	7.5
77.5°	6.0
80°	4.5
82.5°	3.0
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)