

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252081

Luminaire Tested: P3A13R509030DE010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1252081  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R509030DE010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 851.0 lumens  
Efficiency: N/A  
Efficacy: 58.3 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1252081

CATALOG NUMBER: P3A13R509030DE010 E3DLD1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1252081

CATALOG NUMBER: P3A13R509030DE010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 100 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 97  | 96  |  | 91  |
| 2   | 106 | 100 | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 91  | 88  |  | 92  | 89  | 86  |  | 83  |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  |  | 85  | 81  | 78  |  | 75  |
| 4   | 93  | 85  | 78  | 73  | 91  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 69  |
| 5   | 88  | 78  | 72  | 67  | 86  | 77  | 71  | 66  | 75  | 70  | 66  |  | 74  | 69  | 65  |  | 63  |
| 6   | 83  | 73  | 66  | 61  | 81  | 72  | 65  | 61  | 70  | 65  | 60  |  | 69  | 64  | 60  |  | 58  |
| 7   | 78  | 68  | 61  | 56  | 77  | 67  | 61  | 56  | 66  | 60  | 56  |  | 64  | 59  | 55  |  | 53  |
| 8   | 74  | 63  | 57  | 52  | 73  | 63  | 56  | 52  | 61  | 56  | 52  |  | 60  | 55  | 51  |  | 50  |
| 9   | 70  | 59  | 53  | 48  | 69  | 59  | 52  | 48  | 58  | 52  | 48  |  | 57  | 52  | 48  |  | 46  |
| 10  | 66  | 56  | 49  | 45  | 65  | 55  | 49  | 45  | 54  | 49  | 45  |  | 54  | 48  | 45  |  | 43  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 172947 |
| 5°  | 170394 |
| 10° | 162856 |
| 15° | 150807 |
| 20° | 135532 |
| 25° | 119136 |
| 30° | 101332 |
| 35° | 82155  |
| 40° | 61716  |
| 45° | 39756  |
| 50° | 18899  |
| 55° | 14872  |
| 60° | 14078  |
| 65° | 13127  |
| 70° | 11861  |
| 75° | 10675  |
| 80° | 9850   |
| 85° | 9812   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 39756 cd/sqm

TEST NUMBER: P1252081

CATALOG NUMBER: P3A13R509030DE010 E3DLD1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 72.6   | 8.5       |
| 10°-20°   | 185.2  | 21.8      |
| 20°-30°   | 225.0  | 26.4      |
| 30°-40°   | 190.8  | 22.4      |
| 40°-50°   | 99.1   | 11.6      |
| 50°-60°   | 35.8   | 4.2       |
| 60°-70°   | 24.8   | 2.9       |
| 70°-80°   | 13.4   | 1.6       |
| 80°-90°   | 4.2    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 482.8  | 56.7      |
| 0°-40°    | 673.7  | 79.2      |
| 0°-60°    | 808.6  | 95.0      |
| 0°-90°    | 851.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 851.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 789 |      |
| 5°  | 774 | 73   |
| 15° | 664 | 185  |
| 25° | 492 | 225  |
| 35° | 307 | 191  |
| 45° | 128 | 99   |
| 55° | 39  | 36   |
| 65° | 25  | 25   |
| 75° | 13  | 13   |
| 85° | 4   | 4    |
| 90° | 0   |      |

TEST NUMBER: P1252081

CATALOG NUMBER: P3A13R509030DE010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 788.7 |
| 2.5°  | 785.8 |
| 5°    | 774.1 |
| 7.5°  | 756.6 |
| 10°   | 731.4 |
| 12.5° | 699.3 |
| 15°   | 664.3 |
| 17.5° | 624.5 |
| 20°   | 580.8 |
| 22.5° | 536.1 |
| 25°   | 492.4 |
| 27.5° | 446.8 |
| 30°   | 400.2 |
| 32.5° | 353.5 |
| 35°   | 306.9 |
| 37.5° | 261.3 |
| 40°   | 215.6 |
| 42.5° | 171.9 |
| 45°   | 128.2 |
| 47.5° | 85.5  |
| 50°   | 55.4  |
| 52.5° | 42.7  |
| 55°   | 38.9  |
| 57.5° | 35.0  |
| 60°   | 32.1  |
| 62.5° | 28.2  |
| 65°   | 25.3  |
| 67.5° | 21.4  |
| 70°   | 18.5  |
| 72.5° | 15.5  |
| 75°   | 12.6  |
| 77.5° | 9.7   |
| 80°   | 7.8   |
| 82.5° | 5.8   |
| 85°   | 3.9   |
| 87.5° | 1.9   |
| 90°   | 0.0   |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

IRiS

Report Number: SP1-2504-409-28

Test Date: 05/16/2025

Luminaire Tested: LD3A09R159030D010 E3D1H

Data in this report applies to families of products including LD3A

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2504-409-28  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 01/06/2026  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: IRiS  
 Catalog Number: **LD3A09R159030D010 E3D1H**  
 Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI LEDS, E3D1H TRIM

### Spectral Parameters

CCT (K): 3032  
 CIE  $u'$ : 0.2493  
 CIE  $v'$ : 0.5211  
 Duv: 0.0003  
 CIE x: 0.4351  
 CIE y: 0.4042  
 CIE z: 0.1608  
 Peak Wavelength (nm): 615  
 Dominant Wavelength (nm): 582  
 Purity: 51.90029  
 R<sub>f</sub>: 91.6  
 R<sub>g</sub>: 98.2

CRI (Ra): 92.8  
 R1: 93.5  
 R2: 97.3  
 R3: 98.7  
 R4: 93.9  
 R5: 93.6  
 R6: 96.7  
 R7: 90.3  
 R8: 78.4  
 R9: 51.3  
 R10: 93.2  
 R11: 96.4  
 R12: 82.1  
 R13: 94.8  
 R14: 99.6  
 R15: 87.6



### Test Conditions

Stabilization Time: 40M  
 Operation Time: 1H 40M  
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2504-409-28

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 76INCH SPHERE IN0058  | 12/16/2024       | 6/16/2025            |
| Power Meter                    | XITRON INXT2011004    | 1/21/2025        | 1/21/2026            |
| AC Power Source                | CHROMA 61603 IN0063   | 10/22/2024       | 10/22/2025           |
| DC Power Source                | AGILENT E3634A IN0208 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | ONSET IN0085          | 10/22/2024       | 10/22/2025           |
| Room Thermometer               | ONSET IN0046          | 10/22/2024       | 10/22/2025           |

REPORT NUMBER: SP1-2504-409-28

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2504-409-28

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 285                                    | NR                             | 620               | 993                                    | NR                             | 750               | 55                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 338                                    | NR                             | 625               | 970                                    | NR                             | 755               | 47                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 392                                    | NR                             | 630               | 942                                    | NR                             | 760               | 41                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 440                                    | NR                             | 635               | 902                                    | NR                             | 765               | 35                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 478                                    | NR                             | 640               | 855                                    | NR                             | 770               | 30                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 505                                    | NR                             | 645               | 800                                    | NR                             | 775               | 26                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 524                                    | NR                             | 650               | 743                                    | NR                             | 780               | 22                                     | NR                             | 910               | 0                                      | NR                             |
| 395               | 1                                      | NR                             | 525               | 539                                    | NR                             | 655               | 682                                    | NR                             | 785               | 19                                     | NR                             | 915               | 0                                      | NR                             |
| 400               | 2                                      | NR                             | 530               | 554                                    | NR                             | 660               | 621                                    | NR                             | 790               | 16                                     | NR                             | 920               | 0                                      | NR                             |
| 405               | 3                                      | NR                             | 535               | 565                                    | NR                             | 665               | 563                                    | NR                             | 795               | 14                                     | NR                             | 925               | 1                                      | NR                             |
| 410               | 5                                      | NR                             | 540               | 581                                    | NR                             | 670               | 505                                    | NR                             | 800               | 12                                     | NR                             | 930               | 0                                      | NR                             |
| 415               | 10                                     | NR                             | 545               | 593                                    | NR                             | 675               | 451                                    | NR                             | 805               | 10                                     | NR                             | 935               | 0                                      | NR                             |
| 420               | 17                                     | NR                             | 550               | 606                                    | NR                             | 680               | 401                                    | NR                             | 810               | 9                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 32                                     | NR                             | 555               | 623                                    | NR                             | 685               | 356                                    | NR                             | 815               | 8                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 57                                     | NR                             | 560               | 645                                    | NR                             | 690               | 313                                    | NR                             | 820               | 7                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 103                                    | NR                             | 565               | 667                                    | NR                             | 695               | 274                                    | NR                             | 825               | 6                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 175                                    | NR                             | 570               | 699                                    | NR                             | 700               | 238                                    | NR                             | 830               | 5                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 287                                    | NR                             | 575               | 732                                    | NR                             | 705               | 208                                    | NR                             | 835               | 4                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 460                                    | NR                             | 580               | 774                                    | NR                             | 710               | 180                                    | NR                             | 840               | 4                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 550                                    | NR                             | 585               | 816                                    | NR                             | 715               | 157                                    | NR                             | 845               | 3                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 423                                    | NR                             | 590               | 862                                    | NR                             | 720               | 136                                    | NR                             | 850               | 3                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 309                                    | NR                             | 595               | 907                                    | NR                             | 725               | 117                                    | NR                             | 855               | 2                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 269                                    | NR                             | 600               | 943                                    | NR                             | 730               | 100                                    | NR                             | 860               | 2                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 229                                    | NR                             | 605               | 974                                    | NR                             | 735               | 86                                     | NR                             | 865               | 2                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 214                                    | NR                             | 610               | 991                                    | NR                             | 740               | 72                                     | NR                             | 870               | 2                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 241                                    | NR                             | 615               | 1000                                   | NR                             | 745               | 62                                     | NR                             | 875               | 1                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2504-409-28

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.44

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 285                         | NR               | 620       | 993                         | NR               | 750       | 55                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 338                         | NR               | 625       | 970                         | NR               | 755       | 47                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 392                         | NR               | 630       | 942                         | NR               | 760       | 41                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 440                         | NR               | 635       | 902                         | NR               | 765       | 35                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 478                         | NR               | 640       | 855                         | NR               | 770       | 30                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 505                         | NR               | 645       | 800                         | NR               | 775       | 26                          | NR               | 905       | 1                           | NR               |
| 390       | 0                           | NR               | 520       | 524                         | NR               | 650       | 743                         | NR               | 780       | 22                          | NR               | 910       | 0                           | NR               |
| 395       | 1                           | NR               | 525       | 539                         | NR               | 655       | 682                         | NR               | 785       | 19                          | NR               | 915       | 0                           | NR               |
| 400       | 2                           | NR               | 530       | 554                         | NR               | 660       | 621                         | NR               | 790       | 16                          | NR               | 920       | 0                           | NR               |
| 405       | 3                           | NR               | 535       | 565                         | NR               | 665       | 563                         | NR               | 795       | 14                          | NR               | 925       | 1                           | NR               |
| 410       | 5                           | NR               | 540       | 581                         | NR               | 670       | 505                         | NR               | 800       | 12                          | NR               | 930       | 0                           | NR               |
| 415       | 10                          | NR               | 545       | 593                         | NR               | 675       | 451                         | NR               | 805       | 10                          | NR               | 935       | 0                           | NR               |
| 420       | 17                          | NR               | 550       | 606                         | NR               | 680       | 401                         | NR               | 810       | 9                           | NR               | 940       | 0                           | NR               |
| 425       | 32                          | NR               | 555       | 623                         | NR               | 685       | 356                         | NR               | 815       | 8                           | NR               | 945       | 0                           | NR               |
| 430       | 57                          | NR               | 560       | 645                         | NR               | 690       | 313                         | NR               | 820       | 7                           | NR               | 950       | 0                           | NR               |
| 435       | 103                         | NR               | 565       | 667                         | NR               | 695       | 274                         | NR               | 825       | 6                           | NR               | 955       | 0                           | NR               |
| 440       | 175                         | NR               | 570       | 699                         | NR               | 700       | 238                         | NR               | 830       | 5                           | NR               | 960       | 0                           | NR               |
| 445       | 287                         | NR               | 575       | 732                         | NR               | 705       | 208                         | NR               | 835       | 4                           | NR               | 965       | 0                           | NR               |
| 450       | 460                         | NR               | 580       | 774                         | NR               | 710       | 180                         | NR               | 840       | 4                           | NR               | 970       | 0                           | NR               |
| 455       | 550                         | NR               | 585       | 816                         | NR               | 715       | 157                         | NR               | 845       | 3                           | NR               | 975       | 0                           | NR               |
| 460       | 423                         | NR               | 590       | 862                         | NR               | 720       | 136                         | NR               | 850       | 3                           | NR               | 980       | 0                           | NR               |
| 465       | 309                         | NR               | 595       | 907                         | NR               | 725       | 117                         | NR               | 855       | 2                           | NR               | 985       | 0                           | NR               |
| 470       | 269                         | NR               | 600       | 943                         | NR               | 730       | 100                         | NR               | 860       | 2                           | NR               | 990       | 0                           | NR               |
| 475       | 229                         | NR               | 605       | 974                         | NR               | 735       | 86                          | NR               | 865       | 2                           | NR               | 995       | 0                           | NR               |
| 480       | 214                         | NR               | 610       | 991                         | NR               | 740       | 72                          | NR               | 870       | 2                           | NR               | 1000      | 0                           | NR               |
| 485       | 241                         | NR               | 615       | 1000                        | NR               | 745       | 62                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2504-409-28

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.84

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 285                                    | NR                             | 620               | 993                                    | NR                             | 750               | 55                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 338                                    | NR                             | 625               | 970                                    | NR                             | 755               | 47                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 392                                    | NR                             | 630               | 942                                    | NR                             | 760               | 41                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 440                                    | NR                             | 635               | 902                                    | NR                             | 765               | 35                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 478                                    | NR                             | 640               | 855                                    | NR                             | 770               | 30                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 505                                    | NR                             | 645               | 800                                    | NR                             | 775               | 26                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 524                                    | NR                             | 650               | 743                                    | NR                             | 780               | 22                                     | NR                             | 910               | 0                                      | NR                             |
| 395               | 1                                      | NR                             | 525               | 539                                    | NR                             | 655               | 682                                    | NR                             | 785               | 19                                     | NR                             | 915               | 0                                      | NR                             |
| 400               | 2                                      | NR                             | 530               | 554                                    | NR                             | 660               | 621                                    | NR                             | 790               | 16                                     | NR                             | 920               | 0                                      | NR                             |
| 405               | 3                                      | NR                             | 535               | 565                                    | NR                             | 665               | 563                                    | NR                             | 795               | 14                                     | NR                             | 925               | 1                                      | NR                             |
| 410               | 5                                      | NR                             | 540               | 581                                    | NR                             | 670               | 505                                    | NR                             | 800               | 12                                     | NR                             | 930               | 0                                      | NR                             |
| 415               | 10                                     | NR                             | 545               | 593                                    | NR                             | 675               | 451                                    | NR                             | 805               | 10                                     | NR                             | 935               | 0                                      | NR                             |
| 420               | 17                                     | NR                             | 550               | 606                                    | NR                             | 680               | 401                                    | NR                             | 810               | 9                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 32                                     | NR                             | 555               | 623                                    | NR                             | 685               | 356                                    | NR                             | 815               | 8                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 57                                     | NR                             | 560               | 645                                    | NR                             | 690               | 313                                    | NR                             | 820               | 7                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 103                                    | NR                             | 565               | 667                                    | NR                             | 695               | 274                                    | NR                             | 825               | 6                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 175                                    | NR                             | 570               | 699                                    | NR                             | 700               | 238                                    | NR                             | 830               | 5                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 287                                    | NR                             | 575               | 732                                    | NR                             | 705               | 208                                    | NR                             | 835               | 4                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 460                                    | NR                             | 580               | 774                                    | NR                             | 710               | 180                                    | NR                             | 840               | 4                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 550                                    | NR                             | 585               | 816                                    | NR                             | 715               | 157                                    | NR                             | 845               | 3                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 423                                    | NR                             | 590               | 862                                    | NR                             | 720               | 136                                    | NR                             | 850               | 3                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 309                                    | NR                             | 595               | 907                                    | NR                             | 725               | 117                                    | NR                             | 855               | 2                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 269                                    | NR                             | 600               | 943                                    | NR                             | 730               | 100                                    | NR                             | 860               | 2                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 229                                    | NR                             | 605               | 974                                    | NR                             | 735               | 86                                     | NR                             | 865               | 2                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 214                                    | NR                             | 610               | 991                                    | NR                             | 740               | 72                                     | NR                             | 870               | 2                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 241                                    | NR                             | 615               | 1000                                   | NR                             | 745               | 62                                     | NR                             | 875               | 1                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2504-409-28

TM-30-18

### Summary

$R_f = 91.6$   
 $R_g = 98.2$   
 $CIE R_a = 92.8$   
 $R_9 = 51.3$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 96 | CES51 = 97 | CES76 = 92 |
| CES02 = 63 | CES27 = 91 | CES52 = 99 | CES77 = 88 |
| CES03 = 32 | CES28 = 98 | CES53 = 98 | CES78 = 88 |
| CES04 = 70 | CES29 = 97 | CES54 = 93 | CES79 = 91 |
| CES05 = 50 | CES30 = 90 | CES55 = 91 | CES80 = 92 |
| CES06 = 51 | CES31 = 97 | CES56 = 94 | CES81 = 78 |
| CES07 = 43 | CES32 = 93 | CES57 = 93 | CES82 = 96 |
| CES08 = 42 | CES33 = 97 | CES58 = 94 | CES83 = 95 |
| CES09 = 29 | CES34 = 97 | CES59 = 97 | CES84 = 95 |
| CES10 = 76 | CES35 = 98 | CES60 = 93 | CES85 = 80 |
| CES11 = 59 | CES36 = 82 | CES61 = 93 | CES86 = 79 |
| CES12 = 65 | CES37 = 98 | CES62 = 87 | CES87 = 91 |
| CES13 = 44 | CES38 = 86 | CES63 = 94 | CES88 = 95 |
| CES14 = 74 | CES39 = 98 | CES64 = 92 | CES89 = 84 |
| CES15 = 72 | CES40 = 97 | CES65 = 89 | CES90 = 94 |
| CES16 = 48 | CES41 = 96 | CES66 = 90 | CES91 = 77 |
| CES17 = 50 | CES42 = 97 | CES67 = 89 | CES92 = 76 |
| CES18 = 57 | CES43 = 96 | CES68 = 91 | CES93 = 86 |
| CES19 = 72 | CES44 = 99 | CES69 = 92 | CES94 = 76 |
| CES20 = 67 | CES45 = 99 | CES70 = 89 | CES95 = 83 |
| CES21 = 86 | CES46 = 96 | CES71 = 85 | CES96 = 91 |
| CES22 = 79 | CES47 = 93 | CES72 = 95 | CES97 = 96 |
| CES23 = 92 | CES48 = 89 | CES73 = 85 | CES98 = 93 |
| CES24 = 90 | CES49 = 97 | CES74 = 90 | CES99 = 89 |
| CES25 = 72 | CES50 = 97 | CES75 = 86 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)