

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426537

Luminaire Tested: P3A13RH9030DE010 E3HY1H

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-5)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13RH9030DE010 E3HY1H
Description: 3in Adjustable LED luminaire with, RH optic, 3000K CCT AND, 90CRI , E3HY1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 635.0 lumens
Efficiency: N/A
Efficacy: 43.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426537

CATALOG NUMBER: P3A13RH9030DE010 E3HY1H

Luminous Intensity Polar Plot



TEST NUMBER: P1426537

CATALOG NUMBER: P3A13RH9030DE010 E3HY1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	103		102	101	99		98
2	109	105	102	99	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	84	79	76	91	84	79	75	82	78	75		81	77	74		80
7	88	80	75	72	87	80	75	71	79	74	71		77	74	71		76
8	85	77	71	68	84	76	71	68	75	71	68		74	70	67		73
9	82	73	68	65	81	73	68	65	72	67	64		71	67	64		70
10	79	70	65	62	78	70	65	62	69	65	61		68	64	61		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	281140
5°	264472
10°	243327
15°	220546
20°	128414
25°	84077
30°	67833
35°	33515
40°	16946
45°	7536
50°	1979
55°	382
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7536 cd/sqm

TEST NUMBER: P1426537

CATALOG NUMBER: P3A13RH9030DE010 E3HY1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.1	17.5
10°-20°	248.6	39.1
20°-30°	165.7	26.1
30°-40°	87.5	13.8
40°-50°	20.6	3.2
50°-60°	1.5	0.2
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	525.4	82.7
0°-40°	612.9	96.5
0°-60°	635.0	100.0
0°-90°	635.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	635.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1282	
5°	1202	111
15°	972	249
25°	348	166
35°	125	87
45°	24	21
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426537

CATALOG NUMBER: P3A13RH9030DE010 E3HY1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1282.1
2.5°	1261.7
5°	1201.5
7.5°	1138.4
10°	1092.8
12.5°	1043.3
15°	971.5
17.5°	780.3
20°	550.3
22.5°	395.0
25°	347.5
27.5°	308.6
30°	267.9
32.5°	199.9
35°	125.2
37.5°	85.4
40°	59.2
42.5°	38.8
45°	24.3
47.5°	13.6
50°	5.8
52.5°	2.9
55°	1.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)