

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253040

Luminaire Tested: P3A24R309030D010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24R309030D010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1231.0 lumens
Efficiency: N/A
Efficacy: 42.7 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253040

CATALOG NUMBER: P3A24R309030D010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1253040

CATALOG NUMBER: P3A24R309030D010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74		
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61		
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58		
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55		
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	420646
5°	407549
10°	367217
15°	303770
20°	235174
25°	176430
30°	128070
35°	85340
40°	52441
45°	30794
50°	18899
55°	15330
60°	13376
65°	10896
70°	9809
75°	9743
80°	7198
85°	9561

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30794 cd/sqm

TEST NUMBER: P1253040

CATALOG NUMBER: P3A24R309030D010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.3	13.8
10°-20°	368.5	29.9
20°-30°	335.3	27.2
30°-40°	202.7	16.5
40°-50°	81.3	6.6
50°-60°	36.0	2.9
60°-70°	21.7	1.8
70°-80°	11.8	1.0
80°-90°	3.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	874.1	71.0
0°-40°	1076.8	87.5
0°-60°	1194.1	97.0
0°-90°	1231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1231.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1918	
5°	1852	170
15°	1338	369
25°	729	335
35°	319	203
45°	99	81
55°	40	36
65°	21	22
75°	12	12
85°	4	3
90°	0	

TEST NUMBER: P1253040

CATALOG NUMBER: P3A24R309030D010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1918.3
1°	1916.4
2°	1908.8
3°	1895.4
4°	1876.4
5°	1851.5
6°	1821.0
7°	1788.5
8°	1746.6
9°	1698.8
10°	1649.2
11°	1591.9
12°	1530.9
13°	1469.8
14°	1403.0
15°	1338.1
17.5°	1168.2
20°	1007.8
22.5°	859.0
25°	729.2
27.5°	610.8
30°	505.8
32.5°	408.5
35°	318.8
37.5°	244.3
40°	183.2
42.5°	133.6
45°	99.3
47.5°	74.4
50°	55.4
52.5°	43.9
55°	40.1
57.5°	34.4
60°	30.5
62.5°	24.8
65°	21.0
67.5°	19.1
70°	15.3
72.5°	13.4
75°	11.5
77.5°	9.5
80°	5.7
82.5°	3.8
85°	3.8
87.5°	1.9



TEST NUMBER: P1253040

CATALOG NUMBER: P3A24R309030D010 E3DLP1LI

CANDELA DISTRIBUTION (continued):



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

IRiS

Report Number: SP1-2508-518-2

Test Date: 09/10/2025

Luminaire Tested: LD3A24R159030D010 E3D1LI

Data in this report applies to families of products including LD3A24R159030D010 E3D1LI

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2508-518-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 09/16/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: IRiS
 Catalog Number: **LD3A24R159030D010 E3D1LI**
 Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM

Spectral Parameters

CCT (K): 3028
 CIE u' : 0.2491
 CIE v' : 0.5229
 Duv: 0.0015
 CIE x: 0.4371
 CIE y: 0.4078
 CIE z: 0.1551
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 582
 Purity: 53.60472
 R_f: 90.8
 R_g: 98.9

CRI (Ra): 91.6
 R1: 92.4
 R2: 94.8
 R3: 96.1
 R4: 93.3
 R5: 91.7
 R6: 94.8
 R7: 91.4
 R8: 78.7
 R9: 48.5
 R10: 86.1
 R11: 94.5
 R12: 79.7
 R13: 92.8
 R14: 96.7
 R15: 86.9



Test Conditions

Stabilization Time: 65M
 Operation Time: 2H 5M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2508-518-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2508-518-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2508-518-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	115	NR	620	398	NR	750	11	NR	880	0	NR
365	0	NR	495	138	NR	625	392	NR	755	10	NR	885	0	NR
370	0	NR	500	165	NR	630	1000	NR	760	9	NR	890	0	NR
375	0	NR	505	190	NR	635	751	NR	765	7	NR	895	0	NR
380	0	NR	510	212	NR	640	261	NR	770	6	NR	900	0	NR
385	0	NR	515	230	NR	645	243	NR	775	5	NR	905	0	NR
390	1	NR	520	242	NR	650	220	NR	780	5	NR	910	0	NR
395	1	NR	525	253	NR	655	183	NR	785	4	NR	915	0	NR
400	2	NR	530	262	NR	660	155	NR	790	4	NR	920	0	NR
405	3	NR	535	270	NR	665	132	NR	795	3	NR	925	0	NR
410	6	NR	540	279	NR	670	121	NR	800	3	NR	930	0	NR
415	10	NR	545	287	NR	675	101	NR	805	2	NR	935	0	NR
420	18	NR	550	296	NR	680	88	NR	810	2	NR	940	0	NR
425	30	NR	555	307	NR	685	76	NR	815	2	NR	945	0	NR
430	48	NR	560	317	NR	690	66	NR	820	2	NR	950	0	NR
435	73	NR	565	327	NR	695	57	NR	825	1	NR	955	0	NR
440	107	NR	570	338	NR	700	49	NR	830	1	NR	960	0	NR
445	147	NR	575	349	NR	705	43	NR	835	1	NR	965	0	NR
450	193	NR	580	361	NR	710	37	NR	840	1	NR	970	0	NR
455	206	NR	585	372	NR	715	32	NR	845	1	NR	975	0	NR
460	170	NR	590	379	NR	720	28	NR	850	1	NR	980	0	NR
465	131	NR	595	380	NR	725	24	NR	855	1	NR	985	0	NR
470	107	NR	600	388	NR	730	20	NR	860	1	NR	990	0	NR
475	94	NR	605	392	NR	735	17	NR	865	1	NR	995	0	NR
480	89	NR	610	451	NR	740	15	NR	870	0	NR	1000	0	NR
485	97	NR	615	511	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2508-518-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.4

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	115	NR	620	398	NR	750	11	NR	880	0	NR
365	0	NR	495	138	NR	625	392	NR	755	10	NR	885	0	NR
370	0	NR	500	165	NR	630	1000	NR	760	9	NR	890	0	NR
375	0	NR	505	190	NR	635	751	NR	765	7	NR	895	0	NR
380	0	NR	510	212	NR	640	261	NR	770	6	NR	900	0	NR
385	0	NR	515	230	NR	645	243	NR	775	5	NR	905	0	NR
390	1	NR	520	242	NR	650	220	NR	780	5	NR	910	0	NR
395	1	NR	525	253	NR	655	183	NR	785	4	NR	915	0	NR
400	2	NR	530	262	NR	660	155	NR	790	4	NR	920	0	NR
405	3	NR	535	270	NR	665	132	NR	795	3	NR	925	0	NR
410	6	NR	540	279	NR	670	121	NR	800	3	NR	930	0	NR
415	10	NR	545	287	NR	675	101	NR	805	2	NR	935	0	NR
420	18	NR	550	296	NR	680	88	NR	810	2	NR	940	0	NR
425	30	NR	555	307	NR	685	76	NR	815	2	NR	945	0	NR
430	48	NR	560	317	NR	690	66	NR	820	2	NR	950	0	NR
435	73	NR	565	327	NR	695	57	NR	825	1	NR	955	0	NR
440	107	NR	570	338	NR	700	49	NR	830	1	NR	960	0	NR
445	147	NR	575	349	NR	705	43	NR	835	1	NR	965	0	NR
450	193	NR	580	361	NR	710	37	NR	840	1	NR	970	0	NR
455	206	NR	585	372	NR	715	32	NR	845	1	NR	975	0	NR
460	170	NR	590	379	NR	720	28	NR	850	1	NR	980	0	NR
465	131	NR	595	380	NR	725	24	NR	855	1	NR	985	0	NR
470	107	NR	600	388	NR	730	20	NR	860	1	NR	990	0	NR
475	94	NR	605	392	NR	735	17	NR	865	1	NR	995	0	NR
480	89	NR	610	451	NR	740	15	NR	870	0	NR	1000	0	NR
485	97	NR	615	511	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2508-518-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.69

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	115	NR	620	398	NR	750	11	NR	880	0	NR
365	0	NR	495	138	NR	625	392	NR	755	10	NR	885	0	NR
370	0	NR	500	165	NR	630	1000	NR	760	9	NR	890	0	NR
375	0	NR	505	190	NR	635	751	NR	765	7	NR	895	0	NR
380	0	NR	510	212	NR	640	261	NR	770	6	NR	900	0	NR
385	0	NR	515	230	NR	645	243	NR	775	5	NR	905	0	NR
390	1	NR	520	242	NR	650	220	NR	780	5	NR	910	0	NR
395	1	NR	525	253	NR	655	183	NR	785	4	NR	915	0	NR
400	2	NR	530	262	NR	660	155	NR	790	4	NR	920	0	NR
405	3	NR	535	270	NR	665	132	NR	795	3	NR	925	0	NR
410	6	NR	540	279	NR	670	121	NR	800	3	NR	930	0	NR
415	10	NR	545	287	NR	675	101	NR	805	2	NR	935	0	NR
420	18	NR	550	296	NR	680	88	NR	810	2	NR	940	0	NR
425	30	NR	555	307	NR	685	76	NR	815	2	NR	945	0	NR
430	48	NR	560	317	NR	690	66	NR	820	2	NR	950	0	NR
435	73	NR	565	327	NR	695	57	NR	825	1	NR	955	0	NR
440	107	NR	570	338	NR	700	49	NR	830	1	NR	960	0	NR
445	147	NR	575	349	NR	705	43	NR	835	1	NR	965	0	NR
450	193	NR	580	361	NR	710	37	NR	840	1	NR	970	0	NR
455	206	NR	585	372	NR	715	32	NR	845	1	NR	975	0	NR
460	170	NR	590	379	NR	720	28	NR	850	1	NR	980	0	NR
465	131	NR	595	380	NR	725	24	NR	855	1	NR	985	0	NR
470	107	NR	600	388	NR	730	20	NR	860	1	NR	990	0	NR
475	94	NR	605	392	NR	735	17	NR	865	1	NR	995	0	NR
480	89	NR	610	451	NR	740	15	NR	870	0	NR	1000	0	NR
485	97	NR	615	511	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2508-518-2


TM-30-18

Summary

$R_f = 90.8$
 $R_g = 98.9$
 $\text{CIE } R_a = 91.6$
 $R_9 = 48.5$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 91	CES51 = 99	CES76 = 88
CES02 = 63	CES27 = 95	CES52 = 98	CES77 = 86
CES03 = 32	CES28 = 95	CES53 = 96	CES78 = 86
CES04 = 70	CES29 = 93	CES54 = 96	CES79 = 90
CES05 = 50	CES30 = 98	CES55 = 95	CES80 = 92
CES06 = 51	CES31 = 94	CES56 = 94	CES81 = 72
CES07 = 43	CES32 = 86	CES57 = 94	CES82 = 96
CES08 = 42	CES33 = 96	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 93	CES59 = 97	CES84 = 95
CES10 = 76	CES35 = 96	CES60 = 95	CES85 = 80
CES11 = 58	CES36 = 88	CES61 = 94	CES86 = 76
CES12 = 65	CES37 = 94	CES62 = 92	CES87 = 92
CES13 = 44	CES38 = 95	CES63 = 92	CES88 = 96
CES14 = 74	CES39 = 98	CES64 = 91	CES89 = 82
CES15 = 72	CES40 = 96	CES65 = 87	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 82
CES17 = 50	CES42 = 93	CES67 = 88	CES92 = 76
CES18 = 57	CES43 = 93	CES68 = 90	CES93 = 85
CES19 = 72	CES44 = 99	CES69 = 92	CES94 = 71
CES20 = 67	CES45 = 96	CES70 = 88	CES95 = 84
CES21 = 86	CES46 = 95	CES71 = 85	CES96 = 91
CES22 = 79	CES47 = 90	CES72 = 95	CES97 = 94
CES23 = 92	CES48 = 93	CES73 = 84	CES98 = 93
CES24 = 91	CES49 = 94	CES74 = 91	CES99 = 89
CES25 = 72	CES50 = 99	CES75 = 86	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)