

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245790

Luminaire Tested: P3A02R459024DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1245790  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R459024DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R45 optic, 2400K CCT AND, 90CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 240.0 lumens  
Efficiency: N/A  
Efficacy: 66.7 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1245790  
CATALOG NUMBER: P3A02R459024DE010 E3DLP1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1245790

CATALOG NUMBER: P3A02R459024DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88				88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83				83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78				78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74				74
6	90	82	77	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70				70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66				66
8	83	74	68	65	82	73	68	65	72	68	64	71	67	64	70	67	64	62				62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59				59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57				57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	90124
5°	88025
10°	80916
15°	68559
20°	53181
25°	37188
30°	23421
35°	13786
40°	7815
45°	3783
50°	1330
55°	1070
60°	1053
65°	986
70°	962
75°	932
80°	758
85°	503

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3783 cd/sqm



TEST NUMBER: P1245790  
 CATALOG NUMBER: P3A02R459024DE010 E3DLP1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.0	15.4
10°-20°	82.9	34.6
20°-30°	70.4	29.3
30°-40°	33.6	14.0
40°-50°	10.1	4.2
50°-60°	2.6	1.1
60°-70°	1.9	0.8
70°-80°	1.1	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	190.4	79.3
0°-40°	224.0	93.3
0°-60°	236.7	98.6
0°-90°	240.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	240.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	411	
5°	400	37
15°	302	83
25°	154	70
35°	52	34
45°	12	10
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1245790  
CATALOG NUMBER: P3A02R459024DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	411.0
2.5°	408.4
5°	399.9
7.5°	385.0
10°	363.4
12.5°	334.6
15°	302.0
17.5°	265.7
20°	227.9
22.5°	189.5
25°	153.7
27.5°	121.1
30°	92.5
32.5°	69.5
35°	51.5
37.5°	38.0
40°	27.3
42.5°	18.9
45°	12.2
47.5°	6.9
50°	3.9
52.5°	3.0
55°	2.8
57.5°	2.6
60°	2.4
62.5°	2.1
65°	1.9
67.5°	1.7
70°	1.5
72.5°	1.3
75°	1.1
77.5°	0.9
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)