

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245905

Luminaire Tested: P3A02R659024DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245905
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R659024DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 149.0 lumens
Efficiency: N/A
Efficacy: 41.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245905

CATALOG NUMBER: P3A02R659024DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1245905

CATALOG NUMBER: P3A02R659024DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62		
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57		
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50		
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37870
5°	36936
10°	34402
15°	30829
20°	26626
25°	22138
30°	17471
35°	12930
40°	8902
45°	5520
50°	3002
55°	1873
60°	1623
65°	1453
70°	1218
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5520 cd/sqm

TEST NUMBER: P1245905

CATALOG NUMBER: P3A02R659024DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.6	10.5
10°-20°	37.7	25.3
20°-30°	41.7	28.0
30°-40°	30.3	20.3
40°-50°	14.2	9.5
50°-60°	4.8	3.2
60°-70°	2.8	1.9
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	95.0	63.8
0°-40°	125.3	84.1
0°-60°	144.3	96.9
0°-90°	149.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	149.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	173	
5°	168	16
15°	136	38
25°	92	42
35°	48	30
45°	18	14
55°	5	5
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1245905

CATALOG NUMBER: P3A02R659024DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	172.7
2.5°	171.6
5°	167.8
7.5°	162.0
10°	154.5
12.5°	145.6
15°	135.8
17.5°	125.0
20°	114.1
22.5°	102.7
25°	91.5
27.5°	80.1
30°	69.0
32.5°	58.2
35°	48.3
37.5°	39.3
40°	31.1
42.5°	23.8
45°	17.8
47.5°	12.9
50°	8.8
52.5°	6.0
55°	4.9
57.5°	4.3
60°	3.7
62.5°	3.2
65°	2.8
67.5°	2.4
70°	1.9
72.5°	1.7
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)